

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250364

Luminaire Tested: **LD8B200D010 ER8B200927 8LBN0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250364
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B200D010 ER8B200927 8LBN0GPH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13261.6 lumens
Efficiency: N/A
Efficacy: 59.4 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 223.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250364

CATALOG NUMBER: LD8B200D010 ER8B200927 8LBN0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250364

CATALOG NUMBER: LD8B200D010 ER8B200927 8LBN0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		79	75	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250364

CATALOG NUMBER: LD8B200D010 ER8B200927 8LBN0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1902.3	14.3
10°-20°	4134.5	31.2
20°-30°	4438.7	33.5
30°-40°	2399.0	18.1
40°-50°	374.3	2.8
50°-60°	10.3	0.1
60°-70°	2.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10475.5	79.0
0°-40°	12874.5	97.1
0°-60°	13259.0	100.0
0°-90°	13261.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13261.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	21191	
5°	20773	###
15°	14762	4135
25°	9839	4439
35°	3768	2399
45°	345	374
55°	0	10
65°	0	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250364

CATALOG NUMBER: LD8B200D010 ER8B200927 8LBN0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	21190.6
1°	21230.8
2°	21210.9
3°	21138.2
4°	20998.7
5°	20772.7
6°	20461.5
7°	20042.9
8°	19518.9
9°	18915.8
10°	18245.0
11°	17541.7
12°	16811.9
13°	16082.8
14°	15405.3
15°	14762.0
16°	14171.4
17°	13600.8
18°	13070.0
19°	12573.0
20°	12094.9
21°	11630.4
22°	11192.2
23°	10754.9
24°	10297.1
25°	9839.0
26°	9374.4
27°	8844.0
28°	8259.8
29°	7663.5
30°	7039.5
31°	6369.4
32°	5698.8
33°	5035.5
34°	4365.6
35°	3768.2
37.5°	2408.3
40°	1393.3
42.5°	743.3
45°	345.3
47.5°	186.2
50°	60.2
52.5°	6.8
55°	0.0
57.5°	6.8



TEST NUMBER: P250364

CATALOG NUMBER: LD8B200D010 ER8B200927 8LBNOGPH

CANDELA DISTRIBUTION (continued):

	0°
60°	6.8
62.5°	0.0
65°	0.0
67.5°	6.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)