

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250511

Luminaire Tested: **LD8B200D010 ER8B200935 8LBM0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250511
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14005)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B200D010 ER8B200935 8LBM0GPH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15971.0 lumens
Efficiency: N/A
Efficacy: 71.5 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 223.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250511

CATALOG NUMBER: LD8B200D010 ER8B200935 8LBM0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250511

CATALOG NUMBER: LD8B200D010 ER8B200935 8LBM0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	624602
5°	608812
10°	545768
15°	486083
20°	443430
25°	402883
30°	330359
35°	217414
40°	108456
45°	40369
50°	12262
55°	1484
60°	857
65°	0
70°	622
75°	2478
80°	0
85°	2441



TEST NUMBER: P250511

CATALOG NUMBER: LD8B200D010 ER8B200935 8LBM0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1803.3	11.3
10°-20°	4287.6	26.8
20°-30°	5341.6	33.4
30°-40°	3603.0	22.6
40°-50°	852.0	5.3
50°-60°	62.3	0.4
60°-70°	11.1	0.1
70°-80°	8.2	0.1
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	11432.5	71.6
0°-40°	15035.6	94.1
0°-60°	15949.8	99.9
0°-90°	15971.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	15971.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	20255	
5°	19668	###
15°	15226	4288
25°	11841	5342
35°	5776	3603
45°	926	852
55°	28	62
65°	0	11
75°	21	8
85°	7	2
90°	0	



TEST NUMBER: P250511

CATALOG NUMBER: LD8B200D010 ER8B200935 8LBM0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	20255.4
2.5°	20220.9
5°	19668.2
7.5°	18666.5
10°	17430.0
12.5°	16262.4
15°	15226.2
17.5°	14334.9
20°	13512.9
22.5°	12725.3
25°	11841.1
27.5°	10687.4
30°	9278.0
32.5°	7571.7
35°	5775.5
37.5°	4131.3
40°	2694.3
42.5°	1609.7
45°	925.7
47.5°	518.1
50°	255.6
52.5°	117.5
55°	27.6
57.5°	6.9
60°	13.9
62.5°	20.8
65°	0.0
67.5°	13.9
70°	6.9
72.5°	6.9
75°	20.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	6.9
87.5°	0.0
90°	0.0

(END OF REPORT)