

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250616

Luminaire Tested: **LD8B200D010 ER8B2009727 8LBM0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250616
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13928)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B200D010 ER8B2009727 8LBM0B
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9475.0 lumens
Efficiency: N/A
Efficacy: 42.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 223.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250616

CATALOG NUMBER: LD8B200D010 ER8B2009727 8LBM0B

Luminous Intensity Polar Plot





TEST NUMBER: P250616

CATALOG NUMBER: LD8B200D010 ER8B2009727 8LBM0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	74	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	60	58
9	76	66	61	57	75	66	60	57	65	60	56		64	60	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250616

CATALOG NUMBER: LD8B200D010 ER8B2009727 8LBM0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1079.8	11.4
10°-20°	2507.8	26.5
20°-30°	3181.5	33.6
30°-40°	2179.6	23.0
40°-50°	496.7	5.2
50°-60°	24.7	0.3
60°-70°	1.1	0.0
70°-80°	1.8	0.0
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6769.1	71.4
0°-40°	8948.7	94.4
0°-60°	9470.2	99.9
0°-90°	9475.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9475.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12294	
5°	11873	###
15°	8901	2508
25°	7047	3182
35°	3521	2180
45°	536	497
55°	9	25
65°	5	1
75°	0	2
85°	0	2
90°	0	



TEST NUMBER: P250616

CATALOG NUMBER: LD8B200D010 ER8B2009727 8LBM0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	12294.1
1°	12358.2
2°	12335.3
3°	12243.7
4°	12088.0
5°	11872.9
6°	11611.8
7°	11309.7
8°	10975.4
9°	10618.2
10°	10279.4
11°	9968.1
12°	9633.8
13°	9391.2
14°	9134.7
15°	8901.2
16°	8690.6
17°	8484.5
18°	8292.2
19°	8104.4
20°	7935.0
21°	7761.1
22°	7582.5
23°	7426.9
24°	7252.9
25°	7046.8
26°	6817.8
27°	6552.3
28°	6268.4
29°	5952.5
30°	5604.5
31°	5210.7
32°	4803.2
33°	4377.4
34°	3942.3
35°	3521.1
37.5°	2486.3
40°	1602.6
42.5°	943.2
45°	535.8
47.5°	288.5
50°	146.5
52.5°	27.4
55°	9.2
57.5°	4.6



TEST NUMBER: P250616

CATALOG NUMBER: LD8B200D010 ER8B2009727 8LBM0B

CANDELA DISTRIBUTION (continued):

	0°
60°	0.0
62.5°	0.0
65°	4.6
67.5°	0.0
70°	0.0
72.5°	4.6
75°	0.0
77.5°	0.0
80°	4.6
82.5°	0.0
85°	0.0
87.5°	4.6
90°	0.0

(END OF REPORT)