

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250621

Luminaire Tested: **LD8B150D010 ER8B150930 8LBM0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250621
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13928)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B150D010 ER8B150930 8LBM0B
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8443.3 lumens
Efficiency: N/A
Efficacy: 53.3 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 158.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250621

CATALOG NUMBER: LD8B150D010 ER8B150930 8LBM0B

Luminous Intensity Polar Plot





TEST NUMBER: P250621

CATALOG NUMBER: LD8B150D010 ER8B150930 8LBM0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	74	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	60	58
9	76	66	61	57	75	66	60	57	65	60	56		64	60	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250621

CATALOG NUMBER: LD8B150D010 ER8B150930 8LBM0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	962.3	11.4
10°-20°	2234.7	26.5
20°-30°	2835.1	33.6
30°-40°	1942.2	23.0
40°-50°	442.6	5.2
50°-60°	22.1	0.3
60°-70°	1.0	0.0
70°-80°	1.6	0.0
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6032.1	71.4
0°-40°	7974.3	94.4
0°-60°	8439.0	99.9
0°-90°	8443.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8443.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10956	
5°	10580	962
15°	7932	2235
25°	6280	2835
35°	3138	1942
45°	477	443
55°	8	22
65°	4	1
75°	0	2
85°	0	2
90°	0	



TEST NUMBER: P250621

CATALOG NUMBER: LD8B150D010 ER8B150930 8LBM0B

CANDELA DISTRIBUTION (FULL):

	0°
0°	10955.5
1°	11012.7
2°	10992.2
3°	10910.7
4°	10771.9
5°	10580.2
6°	10347.5
7°	10078.2
8°	9780.4
9°	9462.1
10°	9160.1
11°	8882.7
12°	8585.0
13°	8368.7
14°	8140.1
15°	7932.1
16°	7744.4
17°	7560.7
18°	7389.4
19°	7222.0
20°	7071.0
21°	6916.0
22°	6756.9
23°	6618.3
24°	6463.1
25°	6279.6
26°	6075.5
27°	5838.8
28°	5585.9
29°	5304.3
30°	4994.3
31°	4643.3
32°	4280.2
33°	3900.7
34°	3513.1
35°	3137.7
37.5°	2215.5
40°	1428.0
42.5°	840.5
45°	477.4
47.5°	257.0
50°	130.6
52.5°	24.4
55°	8.2
57.5°	4.1



TEST NUMBER: P250621

CATALOG NUMBER: LD8B150D010 ER8B150930 8LBM0B

CANDELA DISTRIBUTION (continued):

	0°
60°	0.0
62.5°	0.0
65°	4.1
67.5°	0.0
70°	0.0
72.5°	4.1
75°	0.0
77.5°	0.0
80°	4.1
82.5°	0.0
85°	0.0
87.5°	4.1
90°	0.0

(END OF REPORT)