

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246399

Luminaire Tested: **LD8B30D010 ER8B30830 8LBM0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246399  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201569)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B30D010 ER8B30830 8LBM0B  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 3000 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1861.9 lumens  
Efficiency: N/A  
Efficacy: 68.7 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.87  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 27.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246399

CATALOG NUMBER: LD8B30D010 ER8B30830 8LBM0B

### Luminous Intensity Polar Plot





TEST NUMBER: P246399

CATALOG NUMBER: LD8B30D010 ER8B30830 8LBM0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	93	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	74	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	60	58
9	76	66	61	57	75	66	60	57	65	60	56		64	60	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	74485
5°	72207
10°	63238
15°	55838
20°	51156
25°	47120
30°	39221
35°	26050
40°	12672
45°	4575
50°	1386
55°	97
60°	0
65°	58
70°	0
75°	0
80°	142
85°	0



TEST NUMBER: P246399

CATALOG NUMBER: LD8B30D010 ER8B30830 8LBM0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	212.3	11.4
10°-20°	493.5	26.5
20°-30°	624.6	33.5
30°-40°	428.5	23.0
40°-50°	97.4	5.2
50°-60°	4.8	0.3
60°-70°	0.2	0.0
70°-80°	0.3	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1330.4	71.5
0°-40°	1758.9	94.5
0°-60°	1861.1	100.0
0°-90°	1861.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1861.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2416	
5°	2333	212
15°	1749	494
25°	1385	625
35°	692	428
45°	105	97
55°	2	5
65°	1	0
75°	0	0
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P246399

CATALOG NUMBER: LD8B30D010 ER8B30830 8LBM0B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2415.5
2.5°	2415.5
5°	2332.7
7.5°	2190.4
10°	2019.6
12.5°	1869.5
15°	1749.1
17.5°	1648.4
20°	1558.9
22.5°	1474.4
25°	1384.9
27.5°	1260.2
30°	1101.5
32.5°	901.9
35°	692.0
37.5°	488.9
40°	314.8
42.5°	185.2
45°	104.9
47.5°	56.3
50°	28.9
52.5°	5.1
55°	1.8
57.5°	0.8
60°	0.0
62.5°	0.0
65°	0.8
67.5°	0.0
70°	0.0
72.5°	0.8
75°	0.0
77.5°	0.0
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.8
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P246399

CATALOG NUMBER: LD8B30D010 ER8B30830 8LBM0B

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)