

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244671

Luminaire Tested: **LD8B30D010 ER8B30830 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244671
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30830 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2894.0 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244671

CATALOG NUMBER: LD8B30D010 ER8B30830 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244671

CATALOG NUMBER: LD8B30D010 ER8B30830 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| RF | 20 | | | | | 20 | | | | | 20 | | | | | 20 | | | | | 20 | |
| RC | 80 | | | | | 70 | | | | | 50 | | | | | 30 | | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | |
| RCR | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | 100 |
| 1 | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99 | 99 | 98 | 96 | 96 | 94 | 93 | 91 | | | | 91 |
| 2 | 106 | 100 | 95 | 91 | 103 | 98 | 94 | 90 | 95 | 91 | 88 | 92 | 89 | 86 | 89 | 87 | 84 | 83 | | | | 83 |
| 3 | 99 | 91 | 86 | 81 | 97 | 90 | 85 | 80 | 87 | 83 | 79 | 85 | 81 | 78 | 82 | 79 | 76 | 75 | | | | 75 |
| 4 | 93 | 84 | 77 | 72 | 91 | 83 | 77 | 72 | 80 | 75 | 71 | 78 | 74 | 70 | 76 | 73 | 69 | 68 | | | | 68 |
| 5 | 87 | 77 | 70 | 65 | 85 | 76 | 70 | 65 | 74 | 69 | 64 | 73 | 68 | 64 | 71 | 67 | 63 | 62 | | | | 62 |
| 6 | 82 | 71 | 64 | 59 | 80 | 70 | 64 | 59 | 69 | 63 | 59 | 67 | 62 | 58 | 66 | 61 | 58 | 56 | | | | 56 |
| 7 | 77 | 66 | 59 | 54 | 75 | 65 | 59 | 54 | 64 | 58 | 54 | 63 | 57 | 53 | 61 | 57 | 53 | 51 | | | | 51 |
| 8 | 72 | 61 | 54 | 50 | 71 | 61 | 54 | 50 | 60 | 54 | 49 | 58 | 53 | 49 | 57 | 53 | 49 | 47 | | | | 47 |
| 9 | 68 | 57 | 50 | 46 | 67 | 57 | 50 | 46 | 56 | 50 | 46 | 55 | 49 | 45 | 54 | 49 | 45 | 44 | | | | 44 |
| 10 | 65 | 54 | 47 | 42 | 63 | 53 | 47 | 42 | 52 | 46 | 42 | 51 | 46 | 42 | 51 | 46 | 42 | 41 | | | | 41 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 64673 |
| 5° | 63372 |
| 10° | 61365 |
| 15° | 60538 |
| 20° | 60177 |
| 25° | 59416 |
| 30° | 56223 |
| 35° | 46370 |
| 40° | 28955 |
| 45° | 18621 |
| 50° | 14440 |
| 55° | 11112 |
| 60° | 8424 |
| 65° | 5472 |
| 70° | 2344 |
| 75° | 1144 |
| 80° | 515 |
| 85° | 354 |



TEST NUMBER: P244671

CATALOG NUMBER: LD8B30D010 ER8B30830 8LBW0WMH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 192.6 | 6.7 |
| 10°-20° | 535.7 | 18.5 |
| 20°-30° | 798.0 | 27.6 |
| 30°-40° | 741.1 | 25.6 |
| 40°-50° | 350.0 | 12.1 |
| 50°-60° | 188.1 | 6.5 |
| 60°-70° | 75.5 | 2.6 |
| 70°-80° | 11.9 | 0.4 |
| 80°-90° | 1.2 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1526.3 | 52.7 |
| 0°-40° | 2267.4 | 78.3 |
| 0°-60° | 2805.5 | 96.9 |
| 0°-90° | 2894.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2894.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2097 | |
| 5° | 2047 | 193 |
| 15° | 1896 | 536 |
| 25° | 1746 | 798 |
| 35° | 1232 | 741 |
| 45° | 427 | 350 |
| 55° | 207 | 188 |
| 65° | 75 | 75 |
| 75° | 10 | 12 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P244671

CATALOG NUMBER: LD8B30D010 ER8B30830 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2097.3 |
| 2.5° | 2082.9 |
| 5° | 2047.3 |
| 7.5° | 2002.1 |
| 10° | 1959.8 |
| 12.5° | 1925.2 |
| 15° | 1896.3 |
| 17.5° | 1866.5 |
| 20° | 1833.8 |
| 22.5° | 1796.3 |
| 25° | 1746.3 |
| 27.5° | 1676.1 |
| 30° | 1579.0 |
| 32.5° | 1436.7 |
| 35° | 1231.8 |
| 37.5° | 970.3 |
| 40° | 719.3 |
| 42.5° | 535.6 |
| 45° | 427.0 |
| 47.5° | 356.8 |
| 50° | 301.0 |
| 52.5° | 251.0 |
| 55° | 206.7 |
| 57.5° | 168.3 |
| 60° | 136.6 |
| 62.5° | 106.7 |
| 65° | 75.0 |
| 67.5° | 44.2 |
| 70° | 26.0 |
| 72.5° | 15.4 |
| 75° | 9.6 |
| 77.5° | 5.8 |
| 80° | 2.9 |
| 82.5° | 1.9 |
| 85° | 1.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)