

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250600

Luminaire Tested: **LD8B150D010 ER8B150940 8LBM0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250600
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13928)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B150D010 ER8B150940 8LBM0B
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
90 CRI 4000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9107.0 lumens
Efficiency: N/A
Efficacy: 57.5 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.87
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 158.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250600

CATALOG NUMBER: LD8B150D010 ER8B150940 8LBM0B

Luminous Intensity Polar Plot





TEST NUMBER: P250600

CATALOG NUMBER: LD8B150D010 ER8B150940 8LBM0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 114 | 111 | 108 | 106 | 111 | 109 | 107 | 105 | 105 | 103 | 101 | 101 | 100 | 98 | 98 | 97 | 96 | 94 |
| 2 | 108 | 103 | 99 | 96 | 106 | 102 | 98 | 95 | 98 | 95 | 93 | 95 | 93 | 91 | 93 | 91 | 89 | 87 |
| 3 | 103 | 96 | 92 | 88 | 101 | 95 | 91 | 87 | 92 | 89 | 86 | 90 | 87 | 84 | 88 | 85 | 83 | 81 |
| 4 | 98 | 90 | 85 | 81 | 96 | 89 | 84 | 80 | 87 | 83 | 79 | 85 | 81 | 78 | 83 | 80 | 77 | 76 |
| 5 | 93 | 85 | 79 | 75 | 91 | 84 | 78 | 74 | 82 | 77 | 74 | 80 | 76 | 73 | 79 | 75 | 72 | 71 |
| 6 | 88 | 79 | 74 | 69 | 87 | 79 | 73 | 69 | 77 | 72 | 69 | 76 | 71 | 68 | 74 | 71 | 68 | 66 |
| 7 | 84 | 75 | 69 | 65 | 83 | 74 | 68 | 64 | 73 | 68 | 64 | 72 | 67 | 64 | 70 | 66 | 63 | 62 |
| 8 | 80 | 70 | 64 | 60 | 79 | 70 | 64 | 60 | 69 | 64 | 60 | 68 | 63 | 60 | 67 | 63 | 60 | 58 |
| 9 | 76 | 66 | 61 | 57 | 75 | 66 | 60 | 57 | 65 | 60 | 56 | 64 | 60 | 56 | 63 | 59 | 56 | 55 |
| 10 | 72 | 63 | 57 | 53 | 71 | 62 | 57 | 53 | 62 | 57 | 53 | 61 | 56 | 53 | 60 | 56 | 53 | 51 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 364380 |
| 5° | 353239 |
| 10° | 309369 |
| 15° | 273127 |
| 20° | 250279 |
| 25° | 230449 |
| 30° | 191806 |
| 35° | 127399 |
| 40° | 62003 |
| 45° | 22454 |
| 50° | 6759 |
| 55° | 473 |
| 60° | 0 |
| 65° | 321 |
| 70° | 0 |
| 75° | 0 |
| 80° | 781 |
| 85° | 0 |



TEST NUMBER: P250600

CATALOG NUMBER: LD8B150D010 ER8B150940 8LBM0B

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 1037.9 | 11.4 |
| 10°-20° | 2410.4 | 26.5 |
| 20°-30° | 3057.9 | 33.6 |
| 30°-40° | 2094.9 | 23.0 |
| 40°-50° | 477.4 | 5.2 |
| 50°-60° | 23.8 | 0.3 |
| 60°-70° | 1.1 | 0.0 |
| 70°-80° | 1.7 | 0.0 |
| 80°-90° | 1.8 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 6506.2 | 71.4 |
| 0°-40° | 8601.1 | 94.4 |
| 0°-60° | 9102.3 | 99.9 |
| 0°-90° | 9107.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 9107.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 11817 | |
| 5° | 11412 | ### |
| 15° | 8556 | 2410 |
| 25° | 6773 | 3058 |
| 35° | 3384 | 2095 |
| 45° | 515 | 477 |
| 55° | 9 | 24 |
| 65° | 4 | 1 |
| 75° | 0 | 2 |
| 85° | 0 | 2 |
| 90° | 0 | |



TEST NUMBER: P250600

CATALOG NUMBER: LD8B150D010 ER8B150940 8LBM0B

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|---------|
| 0° | 11816.6 |
| 1° | 11878.2 |
| 2° | 11856.2 |
| 3° | 11768.2 |
| 4° | 11618.5 |
| 5° | 11411.7 |
| 6° | 11160.8 |
| 7° | 10870.4 |
| 8° | 10549.1 |
| 9° | 10205.8 |
| 10° | 9880.2 |
| 11° | 9580.9 |
| 12° | 9259.7 |
| 13° | 9026.4 |
| 14° | 8779.9 |
| 15° | 8555.5 |
| 16° | 8353.1 |
| 17° | 8154.9 |
| 18° | 7970.2 |
| 19° | 7789.7 |
| 20° | 7626.9 |
| 21° | 7459.6 |
| 22° | 7288.0 |
| 23° | 7138.4 |
| 24° | 6971.2 |
| 25° | 6773.1 |
| 26° | 6553.0 |
| 27° | 6297.8 |
| 28° | 6024.9 |
| 29° | 5721.3 |
| 30° | 5386.8 |
| 31° | 5008.3 |
| 32° | 4616.6 |
| 33° | 4207.3 |
| 34° | 3789.2 |
| 35° | 3384.3 |
| 37.5° | 2389.7 |
| 40° | 1540.3 |
| 42.5° | 906.6 |
| 45° | 514.9 |
| 47.5° | 277.3 |
| 50° | 140.9 |
| 52.5° | 26.4 |
| 55° | 8.8 |
| 57.5° | 4.4 |



TEST NUMBER: P250600

CATALOG NUMBER: LD8B150D010 ER8B150940 8LBM0B

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|-----|
| 60° | 0.0 |
| 62.5° | 0.0 |
| 65° | 4.4 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 4.4 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 4.4 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 4.4 |
| 90° | 0.0 |

(END OF REPORT)