

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246477

Luminaire Tested: **LD8B30D010 ER8B30835 8LBS0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246477  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-17)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B30D010 ER8B30835 8LBS0B  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 3500 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2818.9 lumens  
Efficiency: N/A  
Efficacy: 104.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 27.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246477

CATALOG NUMBER: LD8B30D010 ER8B30835 8LBS0B

### Luminous Intensity Polar Plot





TEST NUMBER: P246477

CATALOG NUMBER: LD8B30D010 ER8B30835 8LBSOB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	99	94	90	103	98	93	89	94	90	87		91	88	85		88	86	84	82
3	98	90	84	79	96	89	83	79	86	81	77		84	80	76		81	78	75	73
4	92	82	76	70	90	81	75	70	79	73	69		77	72	68		75	71	67	66
5	86	75	68	63	84	74	68	63	72	66	62		71	65	61		69	64	61	59
6	80	69	62	56	78	68	61	56	67	60	56		65	60	55		64	59	55	53
7	75	63	56	51	73	63	56	51	61	55	51		60	54	50		59	54	50	48
8	70	59	51	46	69	58	51	46	57	50	46		56	50	46		54	49	46	44
9	66	54	47	42	65	54	47	42	53	46	42		52	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	39		48	42	38		47	42	38	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	50356
5°	50300
10°	50037
15°	49674
20°	49125
25°	48348
30°	46930
35°	44721
40°	41421
45°	34756
50°	22979
55°	11344
60°	4502
65°	1751
70°	270
75°	0
80°	0
85°	0



TEST NUMBER: P246477

CATALOG NUMBER: LD8B30D010 ER8B30835 8LBS0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	154.2	5.5
10°-20°	438.6	15.6
20°-30°	652.8	23.2
30°-40°	739.4	26.2
40°-50°	597.8	21.2
50°-60°	207.3	7.4
60°-70°	28.4	1.0
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1245.7	44.2
0°-40°	1985.1	70.4
0°-60°	2790.2	99.0
0°-90°	2818.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2818.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1633	
5°	1625	154
15°	1556	439
25°	1421	653
35°	1188	739
45°	797	598
55°	211	207
65°	24	28
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246477

CATALOG NUMBER: LD8B30D010 ER8B30835 8LBS0B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1633
2.5°	1631
5°	1625
7.5°	1613
10°	1598
12.5°	1578
15°	1556
17.5°	1528
20°	1497
22.5°	1461
25°	1421
27.5°	1373
30°	1318
32.5°	1256
35°	1188
37.5°	1113
40°	1029
42.5°	926
45°	797
47.5°	641
50°	479
52.5°	328
55°	211
57.5°	125
60°	73
62.5°	43
65°	24
67.5°	11
70°	3
72.5°	0
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0

(END OF REPORT)