

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246549

Luminaire Tested: **LD8B30D010 ER8B30835 8LBW0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246549
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-48)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30835 8LBW0MW
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3153.0 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246549

CATALOG NUMBER: LD8B30D010 ER8B30835 8LBW0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246549

CATALOG NUMBER: LD8B30D010 ER8B30835 8LBW0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62
5	84	73	66	60	82	72	65	60	70	64	59	68	63	59	67	62	58	56
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47
8	69	58	50	45	68	57	50	45	56	50	45	55	49	45	54	48	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	40
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64420
5°	63335
10°	61343
15°	59925
20°	59071
25°	57912
30°	54375
35°	44382
40°	27493
45°	18621
50°	16407
55°	15483
60°	15356
65°	14885
70°	13344
75°	11557
80°	9767
85°	7784



TEST NUMBER: P246549

CATALOG NUMBER: LD8B30D010 ER8B30835 8LBW0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.5	6.1
10°-20°	530.2	16.8
20°-30°	777.5	24.7
30°-40°	710.7	22.5
40°-50°	351.8	11.2
50°-60°	260.2	8.3
60°-70°	200.0	6.3
70°-80°	104.2	3.3
80°-90°	26.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1500.1	47.6
0°-40°	2210.8	70.1
0°-60°	2822.8	89.5
0°-90°	3153.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3153.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2089	
5°	2046	192
15°	1877	530
25°	1702	777
35°	1179	711
45°	427	352
55°	288	260
65°	204	200
75°	97	104
85°	22	26
90°	0	



TEST NUMBER: P246549

CATALOG NUMBER: LD8B30D010 ER8B30835 8LBW0MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2089.1
2.5°	2078.1
5°	2046.1
7.5°	2003.1
10°	1959.1
12.5°	1916.1
15°	1877.1
17.5°	1840.1
20°	1800.1
22.5°	1755.1
25°	1702.1
27.5°	1629.1
30°	1527.1
32.5°	1384.1
35°	1179.0
37.5°	925.0
40°	683.0
42.5°	517.0
45°	427.0
47.5°	378.0
50°	342.0
52.5°	313.0
55°	288.0
57.5°	267.0
60°	249.0
62.5°	230.0
65°	204.0
67.5°	176.0
70°	148.0
72.5°	122.0
75°	97.0
77.5°	75.0
80°	55.0
82.5°	38.0
85°	22.0
87.5°	8.0
90°	0.0

(END OF REPORT)