

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244677

Luminaire Tested: **LD8B30D010 ER8B30835 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244677
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30835 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3009.0 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244677

CATALOG NUMBER: LD8B30D010 ER8B30835 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244677

CATALOG NUMBER: LD8B30D010 ER8B30835 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79		85	81	78		82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59		67	62	58		66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42		51	46	42		51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	67242
5°	65889
10°	63804
15°	62945
20°	62569
25°	61778
30°	58456
35°	48215
40°	30106
45°	19358
50°	15011
55°	11559
60°	8758
65°	5691
70°	2434
75°	1191
80°	533
85°	354



TEST NUMBER: P244677

CATALOG NUMBER: LD8B30D010 ER8B30835 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.2	6.7
10°-20°	557.0	18.5
20°-30°	829.7	27.6
30°-40°	770.5	25.6
40°-50°	363.9	12.1
50°-60°	195.6	6.5
60°-70°	78.5	2.6
70°-80°	12.3	0.4
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1586.9	52.7
0°-40°	2357.5	78.3
0°-60°	2916.9	96.9
0°-90°	3009.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3009.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2181	
5°	2129	200
15°	1972	557
25°	1816	830
35°	1281	771
45°	444	364
55°	215	196
65°	78	79
75°	10	12
85°	1	1
90°	0	



TEST NUMBER: P244677

CATALOG NUMBER: LD8B30D010 ER8B30835 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2180.6
2.5°	2165.6
5°	2128.6
7.5°	2081.7
10°	2037.7
12.5°	2001.7
15°	1971.7
17.5°	1940.7
20°	1906.7
22.5°	1867.7
25°	1815.7
27.5°	1742.7
30°	1641.7
32.5°	1493.8
35°	1280.8
37.5°	1008.8
40°	747.9
42.5°	556.9
45°	443.9
47.5°	370.9
50°	312.9
52.5°	261.0
55°	215.0
57.5°	175.0
60°	142.0
62.5°	111.0
65°	78.0
67.5°	46.0
70°	27.0
72.5°	16.0
75°	10.0
77.5°	6.0
80°	3.0
82.5°	2.0
85°	1.0
87.5°	0.0
90°	0.0

(END OF REPORT)