

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245265

Luminaire Tested: **LD8B30D010 ER8B30850 8LBM0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245265
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201704)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30850 8LBM0WH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3181.0 lumens
Efficiency: N/A
Efficacy: 117.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245265

CATALOG NUMBER: LD8B30D010 ER8B30850 8LBM0WH

Luminous Intensity Polar Plot





TEST NUMBER: P245265

CATALOG NUMBER: LD8B30D010 ER8B30850 8LBM0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	73		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	75	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67	63	60	59
9	77	67	61	58	76	67	61	57	66	61	57		65	60	57		64	60	57	56
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123136
5°	125500
10°	119656
15°	105656
20°	91561
25°	77364
30°	58139
35°	38928
40°	21802
45°	8757
50°	3032
55°	839
60°	475
65°	416
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P245265

CATALOG NUMBER: LD8B30D010 ER8B30850 8LBM0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.3	11.9
10°-20°	923.1	29.0
20°-30°	1024.4	32.2
30°-40°	649.0	20.4
40°-50°	180.1	5.7
50°-60°	20.6	0.6
60°-70°	4.0	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2326.8	73.1
0°-40°	2975.8	93.6
0°-60°	3176.5	99.9
0°-90°	3181.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3181.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3993	
5°	4054	379
15°	3310	923
25°	2274	1024
35°	1034	649
45°	201	180
55°	16	21
65°	6	4
75°	0	0
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P245265

CATALOG NUMBER: LD8B30D010 ER8B30850 8LBM0WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3993.2
2.5°	4022.8
5°	4054.4
7.5°	3991.2
10°	3821.4
12.5°	3579.3
15°	3309.6
17.5°	3044.8
20°	2790.2
22.5°	2540.3
25°	2273.8
27.5°	1962.2
30°	1632.8
32.5°	1313.8
35°	1034.1
37.5°	781.5
40°	541.6
42.5°	336.8
45°	200.8
47.5°	115.5
50°	63.2
52.5°	30.9
55°	15.6
57.5°	11.8
60°	7.7
62.5°	4.1
65°	5.7
67.5°	2.8
70°	0.0
72.5°	0.8
75°	0.0
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P245265

CATALOG NUMBER: LD8B30D010 ER8B30850 8LBM0WH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)