

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249865

Luminaire Tested: **LD8B150D010 ER8B1509730 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P249865
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13959)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B150D010 ER8B1509730 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10499.1 lumens
Efficiency: N/A
Efficacy: 66.2 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.81
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 158.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P249865

CATALOG NUMBER: LD8B150D010 ER8B1509730 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P249865

CATALOG NUMBER: LD8B150D010 ER8B1509730 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	65	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	55	63	58	54		62	57	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P249865

CATALOG NUMBER: LD8B150D010 ER8B1509730 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1313.1	12.5
10°-20°	3082.8	29.4
20°-30°	3369.4	32.1
30°-40°	2005.1	19.1
40°-50°	550.0	5.2
50°-60°	124.6	1.2
60°-70°	38.5	0.4
70°-80°	11.7	0.1
80°-90°	3.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7765.3	74.0
0°-40°	9770.4	93.1
0°-60°	10445.0	99.5
0°-90°	10499.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10499.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14400	
5°	14169	###
15°	11064	3083
25°	7443	3369
35°	3173	2005
45°	643	550
55°	124	125
65°	39	38
75°	11	12
85°	4	4
90°	0	



TEST NUMBER: P249865

CATALOG NUMBER: LD8B150D010 ER8B1509730 8LBN0H

CANDELA DISTRIBUTION (FULL):

	0°
0°	14400.1
1°	14428.5
2°	14410.7
3°	14375.2
4°	14293.5
5°	14169.1
6°	14009.2
7°	13796.1
8°	13547.4
9°	13259.6
10°	12936.3
11°	12591.6
12°	12222.1
13°	11841.9
14°	11447.6
15°	11063.9
16°	10687.2
17°	10317.7
18°	9948.2
19°	9578.7
20°	9219.9
22.5°	8317.4
25°	7443.4
27.5°	6480.6
30°	5411.1
32.5°	4263.5
35°	3172.8
37.5°	2206.4
40°	1463.8
42.5°	959.3
45°	643.1
47.5°	426.4
50°	284.2
52.5°	174.1
55°	124.4
57.5°	88.8
60°	67.5
62.5°	49.7
65°	39.1
67.5°	24.9
70°	17.8
72.5°	14.2
75°	10.7
77.5°	7.1
80°	7.1



TEST NUMBER: P249865

CATALOG NUMBER: LD8B150D010 ER8B1509730 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
82.5°	3.6
85°	3.6
87.5°	3.6
90°	0.0

(END OF REPORT)