

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250293

Luminaire Tested: **LD8B175D010 ER8B175827 8LBN0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250293
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B175D010 ER8B175827 8LBN0GPH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 2700 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13474.0 lumens
Efficiency: N/A
Efficacy: 76.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 177.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250293

CATALOG NUMBER: LD8B175D010 ER8B175827 8LBN0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250293

CATALOG NUMBER: LD8B175D010 ER8B175827 8LBN0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72	79	75	71	77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	663909
5°	653302
10°	580443
15°	478817
20°	403258
25°	340125
30°	254666
35°	144125
40°	56988
45°	15298
50°	2931
55°	0
60°	426
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P250293

CATALOG NUMBER: LD8B175D010 ER8B175827 8LBN0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1932.7	14.3
10°-20°	4200.7	31.2
20°-30°	4509.8	33.5
30°-40°	2437.4	18.1
40°-50°	380.3	2.8
50°-60°	10.4	0.1
60°-70°	2.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10643.3	79.0
0°-40°	13080.7	97.1
0°-60°	13471.4	100.0
0°-90°	13474.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13474.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	21530	
5°	21106	###
15°	14999	4201
25°	9997	4510
35°	3829	2437
45°	351	380
55°	0	10
65°	0	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250293

CATALOG NUMBER: LD8B175D010 ER8B175827 8LBNOGPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	21530.1
1°	21571.0
2°	21550.7
3°	21476.9
4°	21335.1
5°	21105.5
6°	20789.3
7°	20364.0
8°	19831.6
9°	19218.8
10°	18537.4
11°	17822.7
12°	17081.2
13°	16340.4
14°	15652.2
15°	14998.6
16°	14398.5
17°	13818.7
18°	13279.4
19°	12774.4
20°	12288.7
21°	11816.7
22°	11371.5
23°	10927.3
24°	10462.1
25°	9996.6
26°	9524.6
27°	8985.7
28°	8392.1
29°	7786.3
30°	7152.2
31°	6471.5
32°	5790.1
33°	5116.2
34°	4435.5
35°	3828.6
37.5°	2446.9
40°	1415.7
42.5°	755.2
45°	350.8
47.5°	189.1
50°	61.1
52.5°	6.9
55°	0.0
57.5°	6.9



TEST NUMBER: P250293

CATALOG NUMBER: LD8B175D010 ER8B175827 8LBNOGPH

CANDELA DISTRIBUTION (continued):

	0°
60°	6.9
62.5°	0.0
65°	0.0
67.5°	6.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)