

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250300

Luminaire Tested: **LD8B175D010 ER8B175830 8LBN0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250300
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B175D010 ER8B175830 8LBN0GPH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13811.0 lumens
Efficiency: N/A
Efficacy: 77.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 177.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250300

CATALOG NUMBER: LD8B175D010 ER8B175830 8LBN0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250300

CATALOG NUMBER: LD8B175D010 ER8B175830 8LBN0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72	79	75	71	77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	680514
5°	669643
10°	594963
15°	490792
20°	413345
25°	348635
30°	261036
35°	147727
40°	58413
45°	15682
50°	3003
55°	0
60°	432
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P250300

CATALOG NUMBER: LD8B175D010 ER8B175830 8LBN0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1981.1	14.3
10°-20°	4305.8	31.2
20°-30°	4622.6	33.5
30°-40°	2498.4	18.1
40°-50°	389.8	2.8
50°-60°	10.7	0.1
60°-70°	2.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10909.5	79.0
0°-40°	13407.9	97.1
0°-60°	13808.3	100.0
0°-90°	13811.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13811.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	22069	
5°	21633	###
15°	15374	4306
25°	10247	4623
35°	3924	2498
45°	360	390
55°	0	11
65°	0	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250300

CATALOG NUMBER: LD8B175D010 ER8B175830 8LBNOGPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	22068.6
1°	22110.5
2°	22089.7
3°	22014.1
4°	21868.8
5°	21633.4
6°	21309.3
7°	20873.3
8°	20327.6
9°	19699.5
10°	19001.1
11°	18268.5
12°	17508.4
13°	16749.1
14°	16043.6
15°	15373.7
16°	14758.6
17°	14164.3
18°	13611.5
19°	13093.9
20°	12596.1
21°	12112.2
22°	11655.9
23°	11200.6
24°	10723.8
25°	10246.7
26°	9762.8
27°	9210.4
28°	8602.0
29°	7981.0
30°	7331.1
31°	6633.4
32°	5934.9
33°	5244.2
34°	4546.4
35°	3924.3
37.5°	2508.1
40°	1451.1
42.5°	774.1
45°	359.6
47.5°	193.9
50°	62.6
52.5°	7.0
55°	0.0
57.5°	7.0



TEST NUMBER: P250300

CATALOG NUMBER: LD8B175D010 ER8B175830 8LBNOGPH

CANDELA DISTRIBUTION (continued):

	0°
60°	7.0
62.5°	0.0
65°	0.0
67.5°	7.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)