

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249635

Luminaire Tested: **LD8B175D010 ER8B175850 8LBS0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P249635
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-95)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B175D010 ER8B175850 8LBS0GPH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 18475.0 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.22
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 177.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P249635

CATALOG NUMBER: LD8B175D010 ER8B175850 8LBS0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P249635

CATALOG NUMBER: LD8B175D010 ER8B175850 8LBS0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81
3	98	90	84	79	96	88	83	78	85	81	77	83	79	75	81	77	74	72
4	91	82	75	69	89	80	74	69	78	73	68	76	71	67	74	70	66	65
5	85	75	67	62	83	73	67	62	72	66	61	70	64	60	68	63	60	58
6	79	68	61	56	78	67	60	55	66	59	55	64	59	54	63	58	54	52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47
8	69	58	51	45	68	57	50	45	56	50	45	55	49	45	54	49	45	43
9	65	54	46	42	64	53	46	41	52	46	41	51	45	41	50	45	41	39
10	61	50	43	38	60	49	43	38	48	42	38	47	42	38	47	41	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	327142
5°	326587
10°	325423
15°	322839
20°	318154
25°	310807
30°	299410
35°	282704
40°	257698
45°	210253
50°	152131
55°	96034
60°	51558
65°	23363
70°	7943
75°	3956
80°	2646
85°	1203



TEST NUMBER: P249635

CATALOG NUMBER: LD8B175D010 ER8B175850 8LBS0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1002.2	5.4
10°-20°	2849.3	15.4
20°-30°	4195.9	22.7
30°-40°	4671.8	25.3
40°-50°	3689.7	20.0
50°-60°	1654.3	9.0
60°-70°	365.1	2.0
70°-80°	41.2	0.2
80°-90°	5.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8047.4	43.6
0°-40°	12719.2	68.8
0°-60°	18063.2	97.8
0°-90°	18475.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	18475.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10609	
5°	10551	###
15°	10113	2849
25°	9135	4196
35°	7510	4672
45°	4821	3690
55°	1786	1654
65°	320	365
75°	33	41
85°	3	5
90°	0	



TEST NUMBER: P249635

CATALOG NUMBER: LD8B175D010 ER8B175850 8LBS0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	10609.0
2.5°	10593.0
5°	10550.7
7.5°	10485.5
10°	10392.9
12.5°	10268.2
15°	10112.7
17.5°	9922.9
20°	9695.3
22.5°	9433.4
25°	9134.9
27.5°	8790.7
30°	8408.8
32.5°	7970.8
35°	7509.9
37.5°	7014.7
40°	6401.8
42.5°	5643.6
45°	4821.3
47.5°	3984.2
50°	3171.2
52.5°	2427.8
55°	1786.3
57.5°	1247.7
60°	836.0
62.5°	529.5
65°	320.2
67.5°	178.4
70°	88.1
72.5°	48.0
75°	33.2
77.5°	24.0
80°	14.9
82.5°	8.0
85°	3.4
87.5°	1.1
90°	0.0

(END OF REPORT)