

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243867

Luminaire Tested: **LD8B30D010 ER8B30930 8LBW0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243867
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30930 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2694.9 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243867

CATALOG NUMBER: LD8B30D010 ER8B30930 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243867

CATALOG NUMBER: LD8B30D010 ER8B30930 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P243867

CATALOG NUMBER: LD8B30D010 ER8B30930 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.5	5.8
10°-20°	515.1	19.1
20°-30°	810.5	30.1
30°-40°	771.0	28.6
40°-50°	355.5	13.2
50°-60°	80.7	3.0
60°-70°	5.3	0.2
70°-80°	1.1	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1481.2	55.0
0°-40°	2252.2	83.6
0°-60°	2688.4	99.8
0°-90°	2694.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2694.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1551	
5°	1590	155
15°	1828	515
25°	1778	811
35°	1264	771
45°	435	355
55°	78	81
65°	4	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P243867

CATALOG NUMBER: LD8B30D010 ER8B30930 8LBW0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1550.6
1°	1549.8
2°	1552.8
3°	1561.7
4°	1574.9
5°	1590.4
6°	1609.5
7°	1630.2
8°	1651.6
9°	1676.7
10°	1703.1
11°	1729.7
12°	1757.7
13°	1784.3
14°	1808.6
15°	1827.8
16°	1841.8
17°	1851.3
18°	1855.8
19°	1855.0
20°	1849.9
21°	1841.0
22°	1830.0
23°	1815.2
24°	1798.3
25°	1777.7
26°	1753.4
27°	1722.3
28°	1685.4
29°	1642.7
30°	1593.3
32.5°	1445.1
35°	1263.7
37.5°	1052.8
40°	822.8
42.5°	608.3
45°	435.1
47.5°	308.2
50°	212.3
52.5°	135.6
55°	78.1
57.5°	39.1
60°	16.9
62.5°	6.6
65°	3.7



TEST NUMBER: P243867

CATALOG NUMBER: LD8B30D010 ER8B30930 8LBW0LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	2.2
70°	1.5
72.5°	1.5
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)