

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P248010

Luminaire Tested: **LD8B175D010 ER8B175950 8LBW0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P248010  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-71)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B175D010 ER8B175950 8LBW0WMH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 5000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 16499.0 lumens  
Efficiency: N/A  
Efficacy: 93.1 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 177.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P248010

CATALOG NUMBER: LD8B175D010 ER8B175950 8LBW0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P248010

CATALOG NUMBER: LD8B175D010 ER8B175950 8LBW0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74
4	93	84	77	72	91	82	76	72	80	75	71	78	74	70	76	72	69	67
5	87	77	70	65	85	76	70	65	74	68	64	72	67	64	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47
9	68	57	50	46	67	56	50	46	55	49	45	54	49	45	54	49	45	43
10	64	53	47	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	359009
5°	356579
10°	351834
15°	347510
20°	344092
25°	336893
30°	304776
35°	245158
40°	177327
45°	119825
50°	87210
55°	63809
60°	47321
65°	31528
70°	13984
75°	6326
80°	4439
85°	5166



TEST NUMBER: P248010

CATALOG NUMBER: LD8B175D010 ER8B175950 8LBW0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1090.9	6.6
10°-20°	3072.4	18.6
20°-30°	4486.7	27.2
30°-40°	4035.1	24.5
40°-50°	2206.8	13.4
50°-60°	1094.0	6.6
60°-70°	432.0	2.6
70°-80°	69.6	0.4
80°-90°	11.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8650.0	52.4
0°-40°	12685.1	76.9
0°-60°	15986.0	96.9
0°-90°	16499.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	16499.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11642	
5°	11520	###
15°	10886	3072
25°	9902	4487
35°	6512	4035
45°	2748	2207
55°	1187	1094
65°	432	432
75°	53	70
85°	15	11
90°	0	



TEST NUMBER: P248010

CATALOG NUMBER: LD8B175D010 ER8B175950 8LBW0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	11642.4
2.5°	11610.1
5°	11519.6
7.5°	11401.9
10°	11236.4
12.5°	11060.4
15°	10885.5
17.5°	10698.1
20°	10485.7
22.5°	10243.1
25°	9901.6
27.5°	9326.8
30°	8559.5
32.5°	7592.2
35°	6512.5
37.5°	5434.9
40°	4405.2
42.5°	3477.5
45°	2747.7
47.5°	2202.1
50°	1817.9
52.5°	1479.5
55°	1186.9
57.5°	958.9
60°	767.3
62.5°	607.0
65°	432.1
67.5°	257.2
70°	155.1
72.5°	87.5
75°	53.1
77.5°	34.4
80°	25.0
82.5°	8.3
85°	14.6
87.5°	6.2
90°	0.0

(END OF REPORT)