

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245787

Luminaire Tested: **LD8B30D010 ER8B30935 8LBS0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245787  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B30D010 ER8B30935 8LBS0GPH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 3500 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2613.0 lumens  
Efficiency: N/A  
Efficacy: 96.4 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 27.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245787

CATALOG NUMBER: LD8B30D010 ER8B30935 8LBS0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P245787

CATALOG NUMBER: LD8B30D010 ER8B30935 8LBS0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61		70	65	61		68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50		59	54	50		58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45		55	49	45		54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38		48	42	38		47	42	38	36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	46251
5°	46109
10°	45656
15°	45185
20°	44714
25°	43983
30°	42778
35°	40829
40°	37963
45°	32053
50°	21760
55°	11371
60°	5100
65°	2488
70°	1001
75°	608
80°	462
85°	318



TEST NUMBER: P245787

CATALOG NUMBER: LD8B30D010 ER8B30935 8LBS0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.2	5.4
10°-20°	399.2	15.3
20°-30°	594.3	22.7
30°-40°	675.6	25.9
40°-50°	552.4	21.1
50°-60°	205.9	7.9
60°-70°	37.6	1.4
70°-80°	5.8	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1134.7	43.4
0°-40°	1810.3	69.3
0°-60°	2568.7	98.3
0°-90°	2613.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2613.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1500	
5°	1490	141
15°	1415	399
25°	1293	594
35°	1085	676
45°	735	552
55°	212	206
65°	34	38
75°	5	6
85°	1	1
90°	0	



TEST NUMBER: P245787

CATALOG NUMBER: LD8B30D010 ER8B30935 8LBS0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1499.9
2.5°	1497.3
5°	1489.6
7.5°	1476.0
10°	1458.1
12.5°	1437.6
15°	1415.4
17.5°	1389.9
20°	1362.6
22.5°	1330.2
25°	1292.7
27.5°	1250.0
30°	1201.4
32.5°	1146.0
35°	1084.6
37.5°	1018.9
40°	943.1
42.5°	849.3
45°	735.0
47.5°	597.7
50°	453.6
52.5°	319.8
55°	211.5
57.5°	133.0
60°	82.7
62.5°	52.9
65°	34.1
67.5°	19.6
70°	11.1
72.5°	6.8
75°	5.1
77.5°	3.4
80°	2.6
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)