

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P248052

Luminaire Tested: **LD8B175D010 ER8B1759730 8LBM0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P248052
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13941)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B175D010 ER8B1759730 8LBM0WMH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12773.0 lumens
Efficiency: N/A
Efficacy: 72.1 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.9
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 177.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P248052

CATALOG NUMBER: LD8B175D010 ER8B1759730 8LBM0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P248052

CATALOG NUMBER: LD8B175D010 ER8B1759730 8LBM0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72	79	74	71	77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56
9	74	64	58	54	73	64	58	54	63	58	54	62	57	54	61	57	54	52
10	71	61	55	51	70	60	55	51	60	54	51	59	54	51	58	54	50	49

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P248052

CATALOG NUMBER: LD8B175D010 ER8B1759730 8LBM0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1289.3	10.1
10°-20°	3232.9	25.3
20°-30°	4081.1	32.0
30°-40°	2935.9	23.0
40°-50°	971.7	7.6
50°-60°	211.6	1.7
60°-70°	43.7	0.3
70°-80°	4.6	0.0
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8603.4	67.4
0°-40°	11539.2	90.3
0°-60°	12722.5	99.6
0°-90°	12773.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12773.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14089	
5°	13855	###
15°	11517	3233
25°	9014	4081
35°	4732	2936
45°	1140	972
55°	207	212
65°	39	44
75°	4	5
85°	0	2
90°	0	



TEST NUMBER: P248052

CATALOG NUMBER: LD8B175D010 ER8B1759730 8LBM0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	14089.3
1°	14108.8
2°	14093.2
3°	14046.3
4°	13960.5
5°	13855.0
6°	13710.6
7°	13523.3
8°	13316.3
9°	13089.9
10°	12840.0
11°	12586.3
12°	12309.1
13°	12043.6
14°	11774.2
15°	11516.6
16°	11262.8
17°	11020.8
18°	10778.8
19°	10548.4
20°	10314.2
21°	10076.0
22°	9841.8
23°	9588.0
24°	9314.8
25°	9014.2
26°	8697.9
27°	8346.6
28°	7975.8
29°	7561.9
30°	7132.5
31°	6679.6
32°	6203.3
33°	5703.7
34°	5215.6
35°	4731.5
37.5°	3552.6
40°	2518.1
42.5°	1706.0
45°	1140.0
47.5°	765.1
50°	511.4
52.5°	308.4
55°	206.9
57.5°	144.4



TEST NUMBER: P248052

CATALOG NUMBER: LD8B175D010 ER8B1759730 8LBM0WMH

CANDELA DISTRIBUTION (continued):

	0°
60°	85.9
62.5°	58.6
65°	39.1
67.5°	35.2
70°	3.9
72.5°	7.8
75°	3.9
77.5°	3.9
80°	0.0
82.5°	7.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)