

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244707

Luminaire Tested: **LD8B30D010 ER8B30935 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244707
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30935 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2566.0 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244707

CATALOG NUMBER: LD8B30D010 ER8B30935 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244707

CATALOG NUMBER: LD8B30D010 ER8B30935 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	57343
5°	56191
10°	54411
15°	53677
20°	53358
25°	52683
30°	49849
35°	41115
40°	25674
45°	16510
50°	12804
55°	9854
60°	7469
65°	4852
70°	2074
75°	1013
80°	462
85°	318



TEST NUMBER: P244707

CATALOG NUMBER: LD8B30D010 ER8B30935 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.7	6.7
10°-20°	475.0	18.5
20°-30°	707.5	27.6
30°-40°	657.1	25.6
40°-50°	310.4	12.1
50°-60°	166.7	6.5
60°-70°	66.9	2.6
70°-80°	10.5	0.4
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1353.3	52.7
0°-40°	2010.4	78.3
0°-60°	2487.5	96.9
0°-90°	2566.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2566.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1860	
5°	1815	171
15°	1681	475
25°	1548	708
35°	1092	657
45°	379	310
55°	183	167
65°	66	67
75°	8	11
85°	1	1
90°	0	



TEST NUMBER: P244707

CATALOG NUMBER: LD8B30D010 ER8B30935 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1859.6
2.5°	1846.8
5°	1815.3
7.5°	1775.2
10°	1737.7
12.5°	1707.0
15°	1681.4
17.5°	1655.0
20°	1626.0
22.5°	1592.7
25°	1548.4
27.5°	1486.1
30°	1400.0
32.5°	1273.8
35°	1092.2
37.5°	860.3
40°	637.8
42.5°	474.9
45°	378.6
47.5°	316.3
50°	266.9
52.5°	222.5
55°	183.3
57.5°	149.2
60°	121.1
62.5°	94.6
65°	66.5
67.5°	39.2
70°	23.0
72.5°	13.6
75°	8.5
77.5°	5.1
80°	2.6
82.5°	1.7
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)