

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246441

Luminaire Tested: **LD8B30D010 ER8B30940 8LBM0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246441
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201569)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30940 8LBM0B
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
90 CRI 4000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1724.0 lumens
Efficiency: N/A
Efficacy: 63.6 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.87
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246441

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBM0B

Luminous Intensity Polar Plot





TEST NUMBER: P246441

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBM0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87
3	103	96	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68965
5°	66855
10°	58553
15°	51701
20°	47366
25°	43626
30°	36315
35°	24119
40°	11734
45°	4239
50°	1286
55°	86
60°	0
65°	58
70°	0
75°	0
80°	142
85°	0



TEST NUMBER: P246441

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBM0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.6	11.4
10°-20°	456.9	26.5
20°-30°	578.3	33.5
30°-40°	396.8	23.0
40°-50°	90.2	5.2
50°-60°	4.4	0.3
60°-70°	0.2	0.0
70°-80°	0.3	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1231.8	71.4
0°-40°	1628.5	94.5
0°-60°	1723.2	100.0
0°-90°	1724.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1724.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2236	
5°	2160	197
15°	1620	457
25°	1282	578
35°	641	397
45°	97	90
55°	2	4
65°	1	0
75°	0	0
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P246441

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBM0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	2236.5
2.5°	2236.5
5°	2159.8
7.5°	2028.0
10°	1870.0
12.5°	1730.9
15°	1619.5
17.5°	1526.3
20°	1443.4
22.5°	1365.1
25°	1282.2
27.5°	1166.8
30°	1019.9
32.5°	835.1
35°	640.7
37.5°	452.7
40°	291.5
42.5°	171.5
45°	97.2
47.5°	52.1
50°	26.8
52.5°	4.7
55°	1.6
57.5°	0.8
60°	0.0
62.5°	0.0
65°	0.8
67.5°	0.0
70°	0.0
72.5°	0.8
75°	0.0
77.5°	0.0
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.8
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P246441

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBM0B

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)