

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244785

Luminaire Tested: **LD8B30D010 ER8B30940 8LBN0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244785
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201884)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30940 8LBN0WMH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 4000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2421.0 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244785

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBN0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244785

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBN0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93		96	94	91		93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86		91	88	85		89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80		86	82	79		84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75		81	77	74		80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70		77	73	70		76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66		73	69	66		72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62		70	65	62		69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59		66	62	58		65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56		63	59	55		62	58	55	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	108723
5°	107206
10°	98091
15°	84219
20°	70917
25°	58579
30°	43949
35°	26197
40°	12479
45°	5438
50°	2451
55°	1075
60°	641
65°	350
70°	361
75°	0
80°	142
85°	601



TEST NUMBER: P244785

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBN0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	319.8	13.2
10°-20°	735.1	30.4
20°-30°	779.9	32.2
30°-40°	445.0	18.4
40°-50°	110.3	4.6
50°-60°	21.6	0.9
60°-70°	6.5	0.3
70°-80°	1.5	0.1
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1834.8	75.8
0°-40°	2279.9	94.2
0°-60°	2411.8	99.6
0°-90°	2421.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2421.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3526	
5°	3463	320
15°	2638	735
25°	1722	780
35°	696	445
45°	125	110
55°	20	22
65°	5	7
75°	0	1
85°	2	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P244785

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBN0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3525.8
2.5°	3524.1
5°	3463.4
7.5°	3329.9
10°	3132.7
12.5°	2894.5
15°	2638.1
17.5°	2393.6
20°	2161.1
22.5°	1937.5
25°	1721.7
27.5°	1490.0
30°	1234.3
32.5°	959.5
35°	695.9
37.5°	479.4
40°	310.0
42.5°	196.5
45°	124.7
47.5°	81.5
50°	51.1
52.5°	31.1
55°	20.0
57.5°	16.0
60°	10.4
62.5°	9.6
65°	4.8
67.5°	4.8
70°	4.0
72.5°	2.4
75°	0.0
77.5°	0.8
80°	0.8
82.5°	1.7
85°	1.7
87.5°	0.8
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P244785

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBN0WMH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)