

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244310

Luminaire Tested: **LD8B20D010 ER8B20830 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244310
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27944)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B20830 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1934.1 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.79
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244310

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P244310

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	69	67
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	58		64	60	57	56
10	74	64	59	55	73	64	58	55	63	58	55		62	58	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	91038
5°	84916
10°	73195
15°	63347
20°	55107
25°	47358
30°	37213
35°	21709
40°	10019
45°	5185
50°	2600
55°	1263
60°	648
65°	379
70°	180
75°	155
80°	124
85°	0



TEST NUMBER: P244310

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	248.3	12.8
10°-20°	554.8	28.7
20°-30°	630.8	32.6
30°-40°	370.4	19.2
40°-50°	99.4	5.1
50°-60°	23.6	1.2
60°-70°	5.4	0.3
70°-80°	1.2	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1433.9	74.1
0°-40°	1804.3	93.3
0°-60°	1927.3	99.7
0°-90°	1934.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1934.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2952	
5°	2743	248
15°	1984	555
25°	1392	631
35°	577	370
45°	119	99
55°	24	24
65°	5	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P244310

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2952.3
1°	2935.9
2°	2905.9
3°	2863.4
4°	2808.6
5°	2743.3
6°	2669.5
7°	2585.8
8°	2502.2
9°	2418.0
10°	2337.6
11°	2259.3
12°	2185.5
13°	2116.9
14°	2048.3
15°	1984.3
16°	1921.6
17°	1859.5
18°	1799.4
19°	1738.7
20°	1679.3
21°	1619.8
22°	1563.0
23°	1506.8
24°	1449.4
25°	1391.9
26°	1332.4
27°	1267.8
28°	1199.8
29°	1125.4
30°	1045.1
32.5°	819.7
35°	576.7
37.5°	380.1
40°	248.9
42.5°	171.8
45°	118.9
47.5°	81.6
50°	54.2
52.5°	35.3
55°	23.5
57.5°	15.7
60°	10.5
62.5°	7.2
65°	5.2



TEST NUMBER: P244310

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	3.3
70°	2.0
72.5°	1.3
75°	1.3
77.5°	0.7
80°	0.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)