

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245361

Luminaire Tested: **LD8B30D010 ER8B30940 8LBS0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245361  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B30D010 ER8B30940 8LBS0WH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 4000 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3077.0 lumens  
Efficiency: N/A  
Efficacy: 113.5 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 27.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245361  
CATALOG NUMBER: LD8B30D010 ER8B30940 8LBS0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P245361

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBS0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	53745
5°	53950
10°	54627
15°	55695
20°	56492
25°	56725
30°	54987
35°	50187
40°	43414
45°	34176
50°	22043
55°	10822
60°	4447
65°	1948
70°	559
75°	214
80°	160
85°	0



TEST NUMBER: P245361

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBS0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	166.4	5.4
10°-20°	493.0	16.0
20°-30°	763.4	24.8
30°-40°	827.0	26.9
40°-50°	595.1	19.3
50°-60°	199.1	6.5
60°-70°	30.1	1.0
70°-80°	2.6	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1422.8	46.2
0°-40°	2249.8	73.1
0°-60°	3044.0	98.9
0°-90°	3077.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3077.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1743	
5°	1743	166
15°	1745	493
25°	1667	763
35°	1333	827
45°	784	595
55°	201	199
65°	27	30
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P245361

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBS0WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1742.9
2.5°	1742.9
5°	1742.9
7.5°	1743.7
10°	1744.6
12.5°	1746.4
15°	1744.6
17.5°	1737.5
20°	1721.5
22.5°	1697.4
25°	1667.2
27.5°	1619.1
30°	1544.3
32.5°	1446.3
35°	1333.2
37.5°	1211.2
40°	1078.5
42.5°	936.0
45°	783.7
47.5°	618.9
50°	459.5
52.5°	315.3
55°	201.3
57.5°	120.2
60°	72.1
62.5°	43.6
65°	26.7
67.5°	13.4
70°	6.2
72.5°	2.7
75°	1.8
77.5°	1.8
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)