

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244454

Luminaire Tested: **LD8B20D010 ER8B20830 8LBS0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244454
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B20830 8LBS0H
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2285.0 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244454

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBS0H

Luminous Intensity Polar Plot





TEST NUMBER: P244454

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBSOH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69	76	72	68	74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62	70	65	61	69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56	65	59	55	63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46	55	50	46	54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40889
5°	40754
10°	40446
15°	40161
20°	39887
25°	39362
30°	38145
35°	35992
40°	32710
45°	26916
50°	17942
55°	9344
60°	4403
65°	2313
70°	1154
75°	798
80°	604
85°	460



TEST NUMBER: P244454

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBSOH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.9	5.5
10°-20°	355.1	15.5
20°-30°	531.1	23.2
30°-40°	594.1	26.0
40°-50°	466.1	20.4
50°-60°	170.1	7.4
60°-70°	34.7	1.5
70°-80°	7.4	0.3
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1011.1	44.2
0°-40°	1605.2	70.2
0°-60°	2241.3	98.1
0°-90°	2285.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2285.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1326	
5°	1317	125
15°	1258	355
25°	1157	531
35°	956	594
45°	617	466
55°	174	170
65°	32	35
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P244454

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBS0H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1326.0
2.5°	1324.0
5°	1316.6
7.5°	1305.8
10°	1291.7
12.5°	1275.5
15°	1258.0
17.5°	1238.5
20°	1215.5
22.5°	1188.6
25°	1156.9
27.5°	1117.8
30°	1071.3
32.5°	1016.8
35°	956.1
37.5°	888.1
40°	812.6
42.5°	723.0
45°	617.2
47.5°	497.9
50°	374.0
52.5°	262.1
55°	173.8
57.5°	111.2
60°	71.4
62.5°	47.2
65°	31.7
67.5°	20.2
70°	12.8
72.5°	8.8
75°	6.7
77.5°	4.7
80°	3.4
82.5°	2.0
85°	1.3
87.5°	0.7
90°	0.0

(END OF REPORT)