

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244713

Luminaire Tested: **LD8B30D010 ER8B30940 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244713
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B30940 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 4000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2680.0 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244713

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244713

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	59890
5°	58686
10°	56828
15°	56062
20°	55727
25°	55024
30°	52064
35°	42941
40°	26813
45°	17243
50°	13370
55°	10295
60°	7802
65°	5071
70°	2164
75°	1060
80°	479
85°	318



TEST NUMBER: P244713

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.3	6.7
10°-20°	496.1	18.5
20°-30°	739.0	27.6
30°-40°	686.3	25.6
40°-50°	324.1	12.1
50°-60°	174.2	6.5
60°-70°	69.9	2.6
70°-80°	11.0	0.4
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1413.4	52.7
0°-40°	2099.7	78.3
0°-60°	2598.0	96.9
0°-90°	2680.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2680.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1942	
5°	1896	178
15°	1756	496
25°	1617	739
35°	1141	686
45°	395	324
55°	192	174
65°	70	70
75°	9	11
85°	1	1
90°	0	



TEST NUMBER: P244713

CATALOG NUMBER: LD8B30D010 ER8B30940 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1942.2
2.5°	1928.9
5°	1895.9
7.5°	1854.1
10°	1814.9
12.5°	1782.8
15°	1756.1
17.5°	1728.5
20°	1698.2
22.5°	1663.5
25°	1617.2
27.5°	1552.2
30°	1462.2
32.5°	1330.4
35°	1140.7
37.5°	898.5
40°	666.1
42.5°	496.0
45°	395.4
47.5°	330.4
50°	278.7
52.5°	232.4
55°	191.5
57.5°	155.8
60°	126.5
62.5°	98.8
65°	69.5
67.5°	41.0
70°	24.0
72.5°	14.2
75°	8.9
77.5°	5.3
80°	2.7
82.5°	1.8
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)