

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243806

Luminaire Tested: **LD8B20D010 ER8B20830 8LBW0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243806
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B20830 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2222.0 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243806

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243806

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	39424
5°	40590
10°	43971
15°	48110
20°	50053
25°	49869
30°	46777
35°	39225
40°	27308
45°	15643
50°	8400
55°	3462
60°	863
65°	219
70°	108
75°	71
80°	107
85°	0



TEST NUMBER: P243806

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.2	5.8
10°-20°	424.7	19.1
20°-30°	668.3	30.1
30°-40°	635.7	28.6
40°-50°	293.1	13.2
50°-60°	66.6	3.0
60°-70°	4.4	0.2
70°-80°	0.9	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1221.3	55.0
0°-40°	1857.0	83.6
0°-60°	2216.6	99.8
0°-90°	2222.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2222.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1278	
5°	1311	128
15°	1507	425
25°	1466	668
35°	1042	636
45°	359	293
55°	64	67
65°	3	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P243806

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBW0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1278.5
1°	1277.9
2°	1280.3
3°	1287.6
4°	1298.5
5°	1311.3
6°	1327.1
7°	1344.1
8°	1361.8
9°	1382.4
10°	1404.3
11°	1426.2
12°	1449.3
13°	1471.2
14°	1491.2
15°	1507.0
16°	1518.6
17°	1526.5
18°	1530.2
19°	1529.5
20°	1525.3
21°	1518.0
22°	1508.9
23°	1496.7
24°	1482.7
25°	1465.7
26°	1445.6
27°	1420.1
28°	1389.7
29°	1354.5
30°	1313.7
32.5°	1191.5
35°	1042.0
37.5°	868.1
40°	678.4
42.5°	501.5
45°	358.7
47.5°	254.1
50°	175.1
52.5°	111.9
55°	64.4
57.5°	32.2
60°	14.0
62.5°	5.5
65°	3.0



TEST NUMBER: P243806

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBW0LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.8
70°	1.2
72.5°	1.2
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)