

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244371

Luminaire Tested: **LD8B30D010 ER8B309730 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244371
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27944)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B309730 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2064.0 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244371

CATALOG NUMBER: LD8B30D010 ER8B309730 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P244371

CATALOG NUMBER: LD8B30D010 ER8B309730 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	69	67
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	58		64	60	57	56
10	74	64	59	55	73	64	58	55	63	58	55		62	58	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244371

CATALOG NUMBER: LD8B30D010 ER8B309730 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	265.0	12.8
10°-20°	592.1	28.7
20°-30°	673.2	32.6
30°-40°	395.4	19.2
40°-50°	106.1	5.1
50°-60°	25.2	1.2
60°-70°	5.8	0.3
70°-80°	1.3	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1530.2	74.1
0°-40°	1925.6	93.3
0°-60°	2056.9	99.7
0°-90°	2064.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2064.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3151	
5°	2928	265
15°	2118	592
25°	1485	673
35°	616	395
45°	127	106
55°	25	25
65°	6	6
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P244371

CATALOG NUMBER: LD8B30D010 ER8B309730 8LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	3150.7
1°	3133.3
2°	3101.2
3°	3055.9
4°	2997.4
5°	2927.7
6°	2848.9
7°	2759.7
8°	2670.4
9°	2580.5
10°	2494.8
11°	2411.1
12°	2332.4
13°	2259.2
14°	2186.0
15°	2117.7
16°	2050.8
17°	1984.5
18°	1920.4
19°	1855.6
20°	1792.1
21°	1728.7
22°	1668.1
23°	1608.1
24°	1546.8
25°	1485.4
26°	1422.0
27°	1353.0
28°	1280.5
29°	1201.0
30°	1115.3
32.5°	874.8
35°	615.5
37.5°	405.7
40°	265.6
42.5°	183.3
45°	126.9
47.5°	87.1
50°	57.9
52.5°	37.6
55°	25.1
57.5°	16.7
60°	11.2
62.5°	7.7
65°	5.6



TEST NUMBER: P244371

CATALOG NUMBER: LD8B30D010 ER8B309730 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	3.5
70°	2.1
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)