

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244299

Luminaire Tested: **LD8B30D010 ER8B309730 8LBW0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244299
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27940)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B30D010 ER8B309730 8LBW0H
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2284.0 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.12
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244299

CATALOG NUMBER: LD8B30D010 ER8B309730 8LBW0H

Luminous Intensity Polar Plot





TEST NUMBER: P244299

CATALOG NUMBER: LD8B30D010 ER8B309730 8LBW0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	95	93	92
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83	79	77	75
4	93	84	78	73	91	83	77	72	81	75	71		79	74	71		77	73	70	68
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71	67	63	62
6	82	71	65	60	80	71	64	59	69	63	59		68	62	58		66	62	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		62	57	53	52
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	64	53	47	42	63	53	47	42	52	46	42		51	46	42		50	45	42	40

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244299

CATALOG NUMBER: LD8B30D010 ER8B309730 8LBW0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.3	6.3
10°-20°	414.1	18.1
20°-30°	623.2	27.3
30°-40°	617.0	27.0
40°-50°	313.5	13.7
50°-60°	126.3	5.5
60°-70°	38.3	1.7
70°-80°	6.6	0.3
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1181.6	51.7
0°-40°	1798.5	78.7
0°-60°	2238.3	98.0
0°-90°	2284.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2284.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1532	
5°	1522	144
15°	1468	414
25°	1361	623
35°	1015	617
45°	384	314
55°	136	126
65°	35	38
75°	5	7
85°	1	1
90°	0	



TEST NUMBER: P244299

CATALOG NUMBER: LD8B30D010 ER8B309730 8LBW0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1531.5
1°	1528.2
2°	1525.6
3°	1524.9
4°	1524.3
5°	1522.3
6°	1519.6
7°	1514.3
8°	1506.4
9°	1499.2
10°	1491.2
11°	1484.6
12°	1480.0
13°	1476.7
14°	1472.8
15°	1468.1
16°	1462.2
17°	1454.9
18°	1446.4
19°	1436.5
20°	1425.2
21°	1413.3
22°	1401.5
23°	1388.9
24°	1375.7
25°	1361.2
26°	1345.4
27°	1324.9
28°	1301.1
29°	1272.7
30°	1239.7
32.5°	1143.4
35°	1015.3
37.5°	855.5
40°	677.3
42.5°	511.6
45°	384.2
47.5°	293.8
50°	230.4
52.5°	178.9
55°	136.0
57.5°	101.0
60°	75.9
62.5°	54.1
65°	35.0



TEST NUMBER: P244299

CATALOG NUMBER: LD8B30D010 ER8B309730 8LBW0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	21.8
70°	13.9
72.5°	8.6
75°	5.3
77.5°	3.3
80°	2.0
82.5°	1.3
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)