

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243968

Luminaire Tested: **LD8B20D010 ER8B20850 8LBMOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243968
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-11)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B20850 8LBM0LI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2290.0 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 0.63 / 0.63 / 0.72
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243968

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243968

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	104	102	101	100	99	98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	90	82	77	73	89	81	76	73	80	75	72	79	75	72	77	74	71	70
7	86	78	72	69	85	77	72	68	76	71	68	75	71	68	74	70	67	66
8	83	74	68	65	82	73	68	65	72	68	64	71	67	64	70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	60	59
10	76	67	62	58	75	67	61	58	66	61	58	65	61	58	64	60	58	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123188
5°	117892
10°	104955
15°	84315
20°	66038
25°	53319
30°	41318
35°	23531
40°	8876
45°	3829
50°	1540
55°	575
60°	308
65°	212
70°	126
75°	83
80°	0
85°	0



TEST NUMBER: P243968

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	349.6	15.3
10°-20°	733.4	32.0
20°-30°	717.7	31.3
30°-40°	397.1	17.3
40°-50°	76.8	3.4
50°-60°	11.8	0.5
60°-70°	2.9	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1800.7	78.6
0°-40°	2197.7	96.0
0°-60°	2286.3	99.8
0°-90°	2290.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2290.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3995	
5°	3809	350
15°	2641	733
25°	1567	718
35°	625	397
45°	88	77
55°	11	12
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P243968

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBM0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3994.9
2.5°	3939.9
5°	3808.6
7.5°	3624.5
10°	3351.9
12.5°	3007.2
15°	2641.1
17.5°	2297.9
20°	2012.4
22.5°	1776.2
25°	1567.1
27.5°	1370.2
30°	1160.4
32.5°	914.2
35°	625.1
37.5°	376.1
40°	220.5
42.5°	137.7
45°	87.8
47.5°	54.9
50°	32.1
52.5°	17.8
55°	10.7
57.5°	6.4
60°	5.0
62.5°	3.6
65°	2.9
67.5°	2.1
70°	1.4
72.5°	0.7
75°	0.7
77.5°	0.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)