

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244472

Luminaire Tested: **LD8B20D010 ER8B20850 8LBS0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244472
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B20850 8LBS0H
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2407.0 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244472

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBS0H

Luminous Intensity Polar Plot





TEST NUMBER: P244472

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBS0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69		76	72	68		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56		65	59	55		63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50		60	54	50		59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46		55	50	46		54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43072
5°	42930
10°	42603
15°	42306
20°	42017
25°	41465
30°	40186
35°	37915
40°	34457
45°	28355
50°	18896
55°	9844
60°	4638
65°	2437
70°	1217
75°	846
80°	622
85°	495



TEST NUMBER: P244472

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBS0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.6	5.5
10°-20°	374.0	15.5
20°-30°	559.5	23.2
30°-40°	625.8	26.0
40°-50°	491.0	20.4
50°-60°	179.1	7.4
60°-70°	36.5	1.5
70°-80°	7.8	0.3
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1065.1	44.2
0°-40°	1690.9	70.2
0°-60°	2361.0	98.1
0°-90°	2407.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2407.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1397	
5°	1387	132
15°	1325	374
25°	1219	560
35°	1007	626
45°	650	491
55°	183	179
65°	33	37
75°	7	8
85°	1	2
90°	0	



TEST NUMBER: P244472

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBS0H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1396.8
2.5°	1394.7
5°	1386.9
7.5°	1375.6
10°	1360.6
12.5°	1343.6
15°	1325.2
17.5°	1304.6
20°	1280.4
22.5°	1252.1
25°	1218.7
27.5°	1177.5
30°	1128.6
32.5°	1071.1
35°	1007.2
37.5°	935.5
40°	856.0
42.5°	761.6
45°	650.2
47.5°	524.5
50°	393.9
52.5°	276.1
55°	183.1
57.5°	117.1
60°	75.2
62.5°	49.7
65°	33.4
67.5°	21.3
70°	13.5
72.5°	9.2
75°	7.1
77.5°	5.0
80°	3.5
82.5°	2.1
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)