

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244040

Luminaire Tested: **LD8B20D010 ER8B20850 8LBSOLI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244040  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B20D010 ER8B20850 8LBSOLI  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 5000 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2483.0 lumens  
Efficiency: N/A  
Efficacy: 116.6 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 21.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244040

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBSOLI

### Luminous Intensity Polar Plot





TEST NUMBER: P244040

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBSOLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	99	95	91	103	98	93	90	94	91	88	91	88	86	88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74
4	92	83	76	71	90	82	75	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	63	84	75	68	63	73	67	63	71	66	62	69	65	61	60
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54
7	75	64	57	52	74	63	56	52	62	56	51	61	55	51	59	54	51	49
8	71	59	52	47	69	58	52	47	57	51	47	56	51	46	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41
10	62	51	44	39	61	50	44	39	50	43	39	49	43	39	48	43	39	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	42690
5°	42875
10°	43571
15°	44675
20°	45453
25°	45504
30°	44095
35°	40373
40°	35089
45°	27766
50°	18004
55°	9000
60°	3774
65°	1664
70°	514
75°	250
80°	249
85°	248



TEST NUMBER: P244040

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBSOLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	132.4	5.3
10°-20°	395.4	15.9
20°-30°	612.6	24.7
30°-40°	665.3	26.8
40°-50°	483.4	19.5
50°-60°	164.3	6.6
60°-70°	26.2	1.1
70°-80°	2.8	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1140.4	45.9
0°-40°	1805.7	72.7
0°-60°	2453.4	98.8
0°-90°	2483.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2483.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1384	
5°	1385	132
15°	1399	395
25°	1337	613
35°	1072	665
45°	637	483
55°	167	164
65°	23	26
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P244040

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBSOLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1384.4
2.5°	1384.4
5°	1385.1
7.5°	1387.3
10°	1391.5
12.5°	1396.5
15°	1399.4
17.5°	1396.5
20°	1385.1
22.5°	1364.5
25°	1337.4
27.5°	1296.8
30°	1238.4
32.5°	1160.8
35°	1072.5
37.5°	976.4
40°	871.7
42.5°	758.4
45°	636.7
47.5°	505.6
50°	375.3
52.5°	257.1
55°	167.4
57.5°	101.8
60°	61.2
62.5°	37.7
65°	22.8
67.5°	12.8
70°	5.7
72.5°	3.6
75°	2.1
77.5°	1.4
80°	1.4
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)