

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244456

Luminaire Tested: **LD8B40D010 ER8B40830 8LBS0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244456
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B40D010 ER8B40830 8LBS0H
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4639.0 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244456

CATALOG NUMBER: LD8B40D010 ER8B40830 8LBS0H

Luminous Intensity Polar Plot





TEST NUMBER: P244456

CATALOG NUMBER: LD8B40D010 ER8B40830 8LBSOH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69		76	72	68		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56		65	59	55		63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50		60	54	50		59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46		55	50	46		54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83014
5°	82740
10°	82113
15°	81534
20°	80982
25°	79916
30°	77445
35°	73071
40°	66411
45°	54642
50°	36421
55°	18972
60°	8943
65°	4692
70°	2344
75°	1632
80°	1208
85°	955



TEST NUMBER: P244456

CATALOG NUMBER: LD8B40D010 ER8B40830 8LBSOH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	253.6	5.5
10°-20°	720.8	15.5
20°-30°	1078.3	23.2
30°-40°	1206.1	26.0
40°-50°	946.2	20.4
50°-60°	345.2	7.4
60°-70°	70.4	1.5
70°-80°	15.1	0.3
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2052.7	44.2
0°-40°	3258.8	70.2
0°-60°	4550.3	98.1
0°-90°	4639.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4639.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2692	
5°	2673	254
15°	2554	721
25°	2349	1078
35°	1941	1206
45°	1253	946
55°	353	345
65°	64	70
75°	14	15
85°	3	3
90°	0	



TEST NUMBER: P244456

CATALOG NUMBER: LD8B40D010 ER8B40830 8LBS0H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2692.1
2.5°	2688.0
5°	2673.0
7.5°	2651.1
10°	2622.4
12.5°	2589.5
15°	2554.0
17.5°	2514.3
20°	2467.8
22.5°	2413.1
25°	2348.8
27.5°	2269.4
30°	2175.0
32.5°	2064.2
35°	1941.1
37.5°	1803.0
40°	1649.8
42.5°	1467.8
45°	1253.0
47.5°	1010.9
50°	759.2
52.5°	532.1
55°	352.9
57.5°	225.7
60°	145.0
62.5°	95.8
65°	64.3
67.5°	41.0
70°	26.0
72.5°	17.8
75°	13.7
77.5°	9.6
80°	6.8
82.5°	4.1
85°	2.7
87.5°	1.4
90°	0.0

(END OF REPORT)