

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246272

Luminaire Tested: **LD8B20D010 ER8B20850 8LBW0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246272  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B20D010 ER8B20850 8LBW0B  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 5000 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1429.0 lumens  
Efficiency: N/A  
Efficacy: 67.1 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 21.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246272

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBW0B

### Luminous Intensity Polar Plot





TEST NUMBER: P246272

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBW0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80
4	96	88	83	78	94	87	82	78	85	80	77	83	79	76	81	78	75	74
5	91	82	76	72	89	81	76	71	80	75	71	78	74	70	76	73	70	68
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	65	63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58
8	77	67	61	57	76	67	61	57	66	60	56	65	60	56	64	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51
10	70	59	53	49	68	59	53	49	58	53	49	57	52	49	57	52	49	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	40297
5°	39281
10°	38235
15°	37524
20°	36550
25°	35252
30°	32345
35°	24800
40°	11798
45°	4492
50°	2192
55°	898
60°	222
65°	51
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P246272

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBW0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	119.6	8.4
10°-20°	330.8	23.1
20°-30°	472.3	33.1
30°-40°	391.4	27.4
40°-50°	96.5	6.8
50°-60°	17.4	1.2
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	922.7	64.6
0°-40°	1314.1	92.0
0°-60°	1428.0	99.9
0°-90°	1429.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1429.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1307	
5°	1269	120
15°	1175	331
25°	1036	472
35°	659	391
45°	103	97
55°	17	17
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246272

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBW0B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1306.8
2.5°	1295.9
5°	1269.0
7.5°	1242.9
10°	1221.1
12.5°	1200.1
15°	1175.4
17.5°	1146.4
20°	1113.8
22.5°	1076.7
25°	1036.1
27.5°	981.0
30°	908.4
32.5°	806.1
35°	658.8
37.5°	476.0
40°	293.1
42.5°	170.5
45°	103.0
47.5°	68.2
50°	45.7
52.5°	29.7
55°	16.7
57.5°	8.0
60°	3.6
62.5°	1.5
65°	0.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)