

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243860

Luminaire Tested: **LD8B20D010 ER8B20927 8LBW0LI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P243860  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B20D010 ER8B20927 8LBW0LI  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 2700 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1810.0 lumens  
Efficiency: N/A  
Efficacy: 85.0 lumens/watt  
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 21.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P243860

CATALOG NUMBER: LD8B20D010 ER8B20927 8LBW0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P243860

CATALOG NUMBER: LD8B20D010 ER8B20927 8LBW0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P243860

CATALOG NUMBER: LD8B20D010 ER8B20927 8LBW0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	104.4	5.8
10°-20°	346.0	19.1
20°-30°	544.4	30.1
30°-40°	517.9	28.6
40°-50°	238.8	13.2
50°-60°	54.2	3.0
60°-70°	3.6	0.2
70°-80°	0.7	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	994.9	55.0
0°-40°	1512.8	83.6
0°-60°	1805.7	99.8
0°-90°	1810.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1810.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1042	
5°	1068	104
15°	1228	346
25°	1194	544
35°	849	518
45°	292	239
55°	52	54
65°	2	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P243860

CATALOG NUMBER: LD8B20D010 ER8B20927 8LBW0LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1041.5
1°	1041.0
2°	1043.0
3°	1049.0
4°	1057.8
5°	1068.2
6°	1081.1
7°	1095.0
8°	1109.4
9°	1126.1
10°	1144.0
11°	1161.8
12°	1180.7
13°	1198.5
14°	1214.8
15°	1227.7
16°	1237.2
17°	1243.6
18°	1246.5
19°	1246.0
20°	1242.6
21°	1236.6
22°	1229.2
23°	1219.3
24°	1207.9
25°	1194.1
26°	1177.6
27°	1156.8
28°	1132.1
29°	1103.4
30°	1070.2
32.5°	970.6
35°	848.8
37.5°	707.2
40°	552.7
42.5°	408.6
45°	292.2
47.5°	207.0
50°	142.6
52.5°	91.1
55°	52.5
57.5°	26.2
60°	11.4
62.5°	4.5
65°	2.5



TEST NUMBER: P243860

CATALOG NUMBER: LD8B20D010 ER8B20927 8LBW0LI

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.5
70°	1.0
72.5°	1.0
75°	0.4
77.5°	0.4
80°	0.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)