

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244724

Luminaire Tested: **LD8B20D010 ER8B20927 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244724
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B20927 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1660.5 lumens
Efficiency: N/A
Efficacy: 78.0 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244724

CATALOG NUMBER: LD8B20D010 ER8B20927 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244724

CATALOG NUMBER: LD8B20D010 ER8B20927 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79		85	81	78		82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59		67	62	58		66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42		51	46	42		51	46	42	41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244724

CATALOG NUMBER: LD8B20D010 ER8B20927 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.5	6.7
10°-20°	307.4	18.5
20°-30°	457.9	27.6
30°-40°	425.2	25.6
40°-50°	200.9	12.1
50°-60°	107.9	6.5
60°-70°	43.3	2.6
70°-80°	6.8	0.4
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	875.8	52.7
0°-40°	1301.0	78.3
0°-60°	1609.7	96.9
0°-90°	1660.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1660.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1203	
5°	1175	110
15°	1088	307
25°	1002	458
35°	707	425
45°	245	201
55°	119	108
65°	43	43
75°	6	7
85°	1	1
90°	0	



TEST NUMBER: P244724

CATALOG NUMBER: LD8B20D010 ER8B20927 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1203.4
2.5°	1195.1
5°	1174.7
7.5°	1148.7
10°	1124.4
12.5°	1104.6
15°	1088.1
17.5°	1071.0
20°	1052.2
22.5°	1030.7
25°	1002.0
27.5°	961.8
30°	906.0
32.5°	824.3
35°	706.8
37.5°	556.8
40°	412.8
42.5°	307.3
45°	245.0
47.5°	204.8
50°	172.7
52.5°	144.0
55°	118.6
57.5°	96.5
60°	78.3
62.5°	61.2
65°	43.1
67.5°	25.4
70°	14.8
72.5°	8.8
75°	5.5
77.5°	3.3
80°	1.7
82.5°	1.1
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)