

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244370

Luminaire Tested: **LD8B20D010 ER8B20930 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244370
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27944)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B20930 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1661.3 lumens
Efficiency: N/A
Efficacy: 78.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244370

CATALOG NUMBER: LD8B20D010 ER8B20930 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P244370

CATALOG NUMBER: LD8B20D010 ER8B20930 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	69	67
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	58		64	60	57	56
10	74	64	59	55	73	64	58	55	63	58	55		62	58	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244370

CATALOG NUMBER: LD8B20D010 ER8B20930 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	213.3	12.8
10°-20°	476.6	28.7
20°-30°	541.9	32.6
30°-40°	318.2	19.2
40°-50°	85.4	5.1
50°-60°	20.3	1.2
60°-70°	4.6	0.3
70°-80°	1.0	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1231.7	74.1
0°-40°	1549.9	93.3
0°-60°	1655.6	99.7
0°-90°	1661.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1661.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2536	
5°	2356	213
15°	1704	477
25°	1196	542
35°	495	318
45°	102	85
55°	20	20
65°	4	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P244370

CATALOG NUMBER: LD8B20D010 ER8B20930 8LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2536.0
1°	2522.0
2°	2496.2
3°	2459.7
4°	2412.6
5°	2356.5
6°	2293.1
7°	2221.3
8°	2149.4
9°	2077.1
10°	2008.0
11°	1940.8
12°	1877.3
13°	1818.4
14°	1759.5
15°	1704.5
16°	1650.7
17°	1597.3
18°	1545.7
19°	1493.5
20°	1442.5
21°	1391.5
22°	1342.6
23°	1294.4
24°	1245.0
25°	1195.7
26°	1144.5
27°	1089.1
28°	1030.6
29°	966.8
30°	897.7
32.5°	704.1
35°	495.4
37.5°	326.5
40°	213.8
42.5°	147.5
45°	102.1
47.5°	70.2
50°	46.5
52.5°	30.3
55°	20.2
57.5°	13.5
60°	9.0
62.5°	6.2
65°	4.5



TEST NUMBER: P244370

CATALOG NUMBER: LD8B20D010 ER8B20930 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	2.8
70°	1.7
72.5°	1.1
75°	1.1
77.5°	0.6
80°	0.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)