

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244462

Luminaire Tested: **LD8B40D010 ER8B40835 8LBS0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244462
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B40D010 ER8B40835 8LBS0H
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4824.0 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244462

CATALOG NUMBER: LD8B40D010 ER8B40835 8LBS0H

Luminous Intensity Polar Plot





TEST NUMBER: P244462

CATALOG NUMBER: LD8B40D010 ER8B40835 8LBSOH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69	76	72	68	74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62	70	65	61	69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56	65	59	55	63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46	55	50	46	54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86326
5°	86040
10°	85385
15°	84784
20°	84211
25°	83100
30°	80535
35°	75985
40°	69056
45°	56823
50°	37875
55°	19730
60°	9300
65°	4881
70°	2434
75°	1692
80°	1261
85°	991



TEST NUMBER: P244462

CATALOG NUMBER: LD8B40D010 ER8B40835 8LBSOH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	263.7	5.5
10°-20°	749.6	15.5
20°-30°	1121.3	23.2
30°-40°	1254.2	26.0
40°-50°	983.9	20.4
50°-60°	359.0	7.4
60°-70°	73.2	1.5
70°-80°	15.7	0.3
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2134.6	44.2
0°-40°	3388.8	70.2
0°-60°	4731.8	98.1
0°-90°	4824.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4824.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2800	
5°	2780	264
15°	2656	750
25°	2442	1121
35°	2018	1254
45°	1303	984
55°	367	359
65°	67	73
75°	14	16
85°	3	3
90°	0	



TEST NUMBER: P244462

CATALOG NUMBER: LD8B40D010 ER8B40835 8LBS0H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2799.5
2.5°	2795.2
5°	2779.6
7.5°	2756.8
10°	2726.9
12.5°	2692.8
15°	2655.8
17.5°	2614.6
20°	2566.2
22.5°	2509.3
25°	2442.4
27.5°	2359.9
30°	2261.8
32.5°	2146.6
35°	2018.5
37.5°	1874.9
40°	1715.5
42.5°	1526.4
45°	1303.0
47.5°	1051.2
50°	789.5
52.5°	553.4
55°	367.0
57.5°	234.7
60°	150.8
62.5°	99.6
65°	66.9
67.5°	42.7
70°	27.0
72.5°	18.5
75°	14.2
77.5°	10.0
80°	7.1
82.5°	4.3
85°	2.8
87.5°	1.4
90°	0.0

(END OF REPORT)