

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244730

Luminaire Tested: **LD8B20D010 ER8B20930 8LBW0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244730  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B20D010 ER8B20930 8LBW0WMH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1751.0 lumens  
Efficiency: N/A  
Efficacy: 82.2 lumens/watt  
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 21.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244730

CATALOG NUMBER: LD8B20D010 ER8B20930 8LBW0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244730

CATALOG NUMBER: LD8B20D010 ER8B20930 8LBW0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79		85	81	78		82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59		67	62	58		66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42		51	46	42		51	46	42	41

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P244730

CATALOG NUMBER: LD8B20D010 ER8B20930 8LBW0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.5	6.7
10°-20°	324.1	18.5
20°-30°	482.8	27.6
30°-40°	448.4	25.6
40°-50°	211.8	12.1
50°-60°	113.8	6.5
60°-70°	45.7	2.6
70°-80°	7.2	0.4
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	923.5	52.7
0°-40°	1371.9	78.3
0°-60°	1697.5	96.9
0°-90°	1751.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1751.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1269	
5°	1239	117
15°	1147	324
25°	1056	483
35°	745	448
45°	258	212
55°	125	114
65°	45	46
75°	6	7
85°	1	1
90°	0	



TEST NUMBER: P244730

CATALOG NUMBER: LD8B20D010 ER8B20930 8LBW0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1269.0
2.5°	1260.2
5°	1238.7
7.5°	1211.4
10°	1185.8
12.5°	1164.8
15°	1147.3
17.5°	1129.3
20°	1109.6
22.5°	1086.8
25°	1056.5
27.5°	1014.2
30°	955.3
32.5°	869.2
35°	745.4
37.5°	587.1
40°	435.2
42.5°	324.1
45°	258.3
47.5°	215.9
50°	182.2
52.5°	151.9
55°	125.1
57.5°	101.8
60°	82.6
62.5°	64.6
65°	45.4
67.5°	26.8
70°	15.7
72.5°	9.3
75°	5.8
77.5°	3.5
80°	1.8
82.5°	1.1
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)