

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245576

Luminaire Tested: **LD8B20D010 ER8B20940 8LBW0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245576  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B20D010 ER8B20940 8LBW0GPH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 4000 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1743.0 lumens  
Efficiency: N/A  
Efficacy: 81.8 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 21.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245576

CATALOG NUMBER: LD8B20D010 ER8B20940 8LBW0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P245576

CATALOG NUMBER: LD8B20D010 ER8B20940 8LBW0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66	74	70	66	73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51	60	55	51	59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	41851
5°	40863
10°	39582
15°	39008
20°	38548
25°	37723
30°	35333
35°	28851
40°	17225
45°	10344
50°	7455
55°	5075
60°	3182
65°	1561
70°	397
75°	155
80°	107
85°	0



TEST NUMBER: P245576

CATALOG NUMBER: LD8B20D010 ER8B20940 8LBW0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	124.2	7.1
10°-20°	344.8	19.8
20°-30°	506.4	29.1
30°-40°	459.1	26.3
40°-50°	196.5	11.3
50°-60°	87.0	5.0
60°-70°	23.2	1.3
70°-80°	1.8	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	975.4	56.0
0°-40°	1434.5	82.3
0°-60°	1717.9	98.6
0°-90°	1743.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1743.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1357	
5°	1320	124
15°	1222	345
25°	1109	506
35°	766	459
45°	237	197
55°	94	87
65°	21	23
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P245576

CATALOG NUMBER: LD8B20D010 ER8B20940 8LBW0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1357.2
2.5°	1346.5
5°	1320.1
7.5°	1289.9
10°	1264.1
12.5°	1242.7
15°	1221.9
17.5°	1199.9
20°	1174.7
22.5°	1145.1
25°	1108.7
27.5°	1059.6
30°	992.3
32.5°	897.9
35°	766.4
37.5°	594.0
40°	427.9
42.5°	308.9
45°	237.2
47.5°	191.3
50°	155.4
52.5°	123.3
55°	94.4
57.5°	70.5
60°	51.6
62.5°	35.9
65°	21.4
67.5°	9.4
70°	4.4
72.5°	2.5
75°	1.3
77.5°	0.6
80°	0.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)