

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245698

Luminaire Tested: **LD8B40D010 ER8B40850 8LBM0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245698
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201629)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B40D010 ER8B40850 8LBM0GPH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3924.0 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245698

CATALOG NUMBER: LD8B40D010 ER8B40850 8LBM0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245698

CATALOG NUMBER: LD8B40D010 ER8B40850 8LBM0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	153488
5°	149592
10°	134131
15°	119438
20°	108980
25°	98969
30°	81165
35°	53443
40°	26632
45°	9904
50°	3013
55°	339
60°	204
65°	0
70°	144
75°	584
80°	0
85°	566



TEST NUMBER: P245698

CATALOG NUMBER: LD8B40D010 ER8B40850 8LBM0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	443.1	11.3
10°-20°	1053.5	26.8
20°-30°	1312.3	33.4
30°-40°	885.6	22.6
40°-50°	209.3	5.3
50°-60°	15.2	0.4
60°-70°	2.6	0.1
70°-80°	1.9	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2809.0	71.6
0°-40°	3694.5	94.2
0°-60°	3919.0	99.9
0°-90°	3924.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3924.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4978	
5°	4833	443
15°	3741	1054
25°	2909	1312
35°	1420	886
45°	227	209
55°	6	15
65°	0	3
75°	5	2
85°	2	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P245698

CATALOG NUMBER: LD8B40D010 ER8B40850 8LBM0GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4977.5
2.5°	4969.6
5°	4832.7
7.5°	4586.3
10°	4283.7
12.5°	3995.6
15°	3741.3
17.5°	3522.1
20°	3321.0
22.5°	3126.2
25°	2908.8
27.5°	2625.5
30°	2279.5
32.5°	1860.9
35°	1419.7
37.5°	1015.9
40°	661.6
42.5°	395.9
45°	227.1
47.5°	127.2
50°	62.8
52.5°	29.0
55°	6.3
57.5°	1.6
60°	3.3
62.5°	4.9
65°	0.0
67.5°	3.3
70°	1.6
72.5°	1.6
75°	4.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	1.6
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P245698

CATALOG NUMBER: LD8B40D010 ER8B40850 8LBM0GPH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)