

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244436

Luminaire Tested: **LD8B20D010 ER8B209727 8LBM0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244436
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27951)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B209727 8LBM0H
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1485.0 lumens
Efficiency: N/A
Efficacy: 69.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244436

CATALOG NUMBER: LD8B20D010 ER8B209727 8LBM0H

Luminous Intensity Polar Plot





TEST NUMBER: P244436

CATALOG NUMBER: LD8B20D010 ER8B209727 8LBM0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86	83	80	79
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80	77	74	73
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75	72	69	67
6	85	76	70	65	84	75	69	65	74	68	64		72	68	64		71	67	64	62
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67	62	59	58
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63	58	55	54
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59	55	51	50
10	69	59	53	49	68	58	53	49	58	52	48		57	52	48		56	51	48	47

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244436

CATALOG NUMBER: LD8B20D010 ER8B209727 8LBM0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.1	9.2
10°-20°	345.0	23.2
20°-30°	460.3	31.0
30°-40°	354.8	23.9
40°-50°	132.3	8.9
50°-60°	43.3	2.9
60°-70°	10.0	0.7
70°-80°	2.0	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	942.4	63.5
0°-40°	1297.1	87.3
0°-60°	1472.7	99.2
0°-90°	1485.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1485.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1556	
5°	1484	137
15°	1227	345
25°	1013	460
35°	577	355
45°	161	132
55°	45	43
65°	9	10
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P244436

CATALOG NUMBER: LD8B20D010 ER8B209727 8LBM0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1556.1
1°	1549.3
2°	1538.0
3°	1523.4
4°	1505.7
5°	1484.4
6°	1460.3
7°	1432.6
8°	1403.2
9°	1372.7
10°	1344.6
11°	1317.7
12°	1292.5
13°	1269.4
14°	1248.1
15°	1227.2
16°	1205.9
17°	1185.3
18°	1164.0
19°	1143.1
20°	1122.9
21°	1102.0
22°	1081.7
23°	1060.4
24°	1038.1
25°	1013.3
26°	985.9
27°	955.8
28°	922.4
29°	885.2
30°	844.4
32.5°	724.8
35°	577.2
37.5°	427.5
40°	302.6
42.5°	216.8
45°	160.7
47.5°	121.0
50°	89.4
52.5°	63.9
55°	45.4
57.5°	31.2
60°	20.6
62.5°	13.5
65°	8.9



TEST NUMBER: P244436

CATALOG NUMBER: LD8B20D010 ER8B209727 8LBM0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	6.0
70°	3.9
72.5°	2.5
75°	1.8
77.5°	1.1
80°	0.7
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)