

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246596

Luminaire Tested: **LD8B20D010 ER8B209727 8LBW0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246596
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-48)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B209727 8LBW0MW
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1549.0 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246596

CATALOG NUMBER: LD8B20D010 ER8B209727 8LBW0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246596

CATALOG NUMBER: LD8B20D010 ER8B209727 8LBW0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84		88	85	82		86	83	80	78
3	96	88	81	76	94	86	80	75	83	78	74		81	76	73		78	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66		74	69	65		72	68	64	62
5	84	73	66	60	82	72	65	60	70	64	59		68	63	59		67	62	58	56
6	79	67	60	54	77	66	59	54	65	58	54		63	58	53		62	57	53	51
7	74	62	55	49	72	61	54	49	60	54	49		59	53	49		57	52	48	47
8	69	58	50	45	68	57	50	45	56	50	45		55	49	45		54	48	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P246596

CATALOG NUMBER: LD8B20D010 ER8B209727 8LBW0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	6.1
10°-20°	260.5	16.8
20°-30°	382.0	24.7
30°-40°	349.2	22.5
40°-50°	172.9	11.2
50°-60°	127.8	8.3
60°-70°	98.2	6.3
70°-80°	51.2	3.3
80°-90°	12.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	737.0	47.6
0°-40°	1086.1	70.1
0°-60°	1386.8	89.5
0°-90°	1549.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1549.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1026	
5°	1005	95
15°	922	260
25°	836	382
35°	579	349
45°	210	173
55°	142	128
65°	100	98
75°	48	51
85°	11	13
90°	0	



TEST NUMBER: P246596

CATALOG NUMBER: LD8B20D010 ER8B209727 8LBW0MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1026.3
2.5°	1020.9
5°	1005.2
7.5°	984.1
10°	962.5
12.5°	941.3
15°	922.2
17.5°	904.0
20°	884.3
22.5°	862.2
25°	836.2
27.5°	800.3
30°	750.2
32.5°	680.0
35°	579.2
37.5°	454.5
40°	335.6
42.5°	254.0
45°	209.8
47.5°	185.7
50°	168.0
52.5°	153.8
55°	141.5
57.5°	131.2
60°	122.3
62.5°	113.0
65°	100.2
67.5°	86.5
70°	72.7
72.5°	59.9
75°	47.7
77.5°	36.8
80°	27.0
82.5°	18.7
85°	10.8
87.5°	3.9
90°	0.0

(END OF REPORT)