

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243862

Luminaire Tested: **LD8B40D010 ER8B40927 8LBW0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243862
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B40D010 ER8B40927 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3637.1 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243862

CATALOG NUMBER: LD8B40D010 ER8B40927 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243862

CATALOG NUMBER: LD8B40D010 ER8B40927 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P243862

CATALOG NUMBER: LD8B40D010 ER8B40927 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.8	5.8
10°-20°	695.3	19.1
20°-30°	1094.0	30.1
30°-40°	1040.6	28.6
40°-50°	479.7	13.2
50°-60°	109.0	3.0
60°-70°	7.2	0.2
70°-80°	1.4	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1999.1	55.0
0°-40°	3039.7	83.6
0°-60°	3628.4	99.8
0°-90°	3637.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3637.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2093	
5°	2146	210
15°	2467	695
25°	2399	1094
35°	1706	1041
45°	587	480
55°	106	109
65°	5	7
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P243862

CATALOG NUMBER: LD8B40D010 ER8B40927 8LBW0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	2092.7
1°	2091.7
2°	2095.6
3°	2107.6
4°	2125.6
5°	2146.4
6°	2172.3
7°	2200.2
8°	2229.0
9°	2262.8
10°	2298.7
11°	2334.5
12°	2372.3
13°	2408.2
14°	2441.0
15°	2466.9
16°	2485.8
17°	2498.7
18°	2504.7
19°	2503.7
20°	2496.7
21°	2484.8
22°	2469.8
23°	2449.9
24°	2427.1
25°	2399.2
26°	2366.3
27°	2324.6
28°	2274.8
29°	2217.0
30°	2150.4
32.5°	1950.4
35°	1705.6
37.5°	1421.0
40°	1110.5
42.5°	820.9
45°	587.1
47.5°	415.9
50°	286.5
52.5°	183.2
55°	105.5
57.5°	52.8
60°	22.8
62.5°	9.0
65°	5.0



TEST NUMBER: P243862

CATALOG NUMBER: LD8B40D010 ER8B40927 8LBW0LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	3.0
70°	2.0
72.5°	2.0
75°	1.0
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)