

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244300

Luminaire Tested: **LD8B40D010 ER8B40930 8LBW0H**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244300  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27940)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B40D010 ER8B40930 8LBW0H  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3642.2 lumens  
Efficiency: N/A  
Efficacy: 89.1 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.12  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 40.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244300

CATALOG NUMBER: LD8B40D010 ER8B40930 8LBW0H

### Luminous Intensity Polar Plot





TEST NUMBER: P244300

CATALOG NUMBER: LD8B40D010 ER8B40930 8LBW0H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	95	93	92
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83	79	77	75
4	93	84	78	73	91	83	77	72	81	75	71		79	74	71		77	73	70	68
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71	67	63	62
6	82	71	65	60	80	71	64	59	69	63	59		68	62	58		66	62	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		62	57	53	52
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	64	53	47	42	63	53	47	42	52	46	42		51	46	42		50	45	42	40

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P244300

CATALOG NUMBER: LD8B40D010 ER8B40930 8LBW0H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	230.1	6.3
10°-20°	660.3	18.1
20°-30°	993.7	27.3
30°-40°	983.9	27.0
40°-50°	499.9	13.7
50°-60°	201.4	5.5
60°-70°	61.0	1.7
70°-80°	10.5	0.3
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1884.2	51.7
0°-40°	2868.1	78.7
0°-60°	3569.4	98.0
0°-90°	3642.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3642.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2442	
5°	2427	230
15°	2341	660
25°	2171	994
35°	1619	984
45°	613	500
55°	217	201
65°	56	61
75°	8	11
85°	1	1
90°	0	



TEST NUMBER: P244300

CATALOG NUMBER: LD8B40D010 ER8B40930 8LBW0H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2442.2
1°	2436.9
2°	2432.7
3°	2431.7
4°	2430.7
5°	2427.4
6°	2423.3
7°	2414.9
8°	2402.2
9°	2390.6
10°	2378.0
11°	2367.4
12°	2360.0
13°	2354.8
14°	2348.5
15°	2341.1
16°	2331.7
17°	2320.1
18°	2306.3
19°	2290.7
20°	2272.7
21°	2253.8
22°	2234.8
23°	2214.9
24°	2193.8
25°	2170.6
26°	2145.4
27°	2112.7
28°	2074.9
29°	2029.6
30°	1976.9
32.5°	1823.2
35°	1619.1
37.5°	1364.3
40°	1080.1
42.5°	815.9
45°	612.6
47.5°	468.5
50°	367.4
52.5°	285.3
55°	216.8
57.5°	161.1
60°	121.1
62.5°	86.3
65°	55.8



TEST NUMBER: P244300

CATALOG NUMBER: LD8B40D010 ER8B40930 8LBW0H

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	34.8
70°	22.1
72.5°	13.7
75°	8.4
77.5°	5.3
80°	3.1
82.5°	2.1
85°	1.0
87.5°	0.0
90°	0.0

(END OF REPORT)