

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245356

Luminaire Tested: **LD8B40D010 ER8B40935 8LBS0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245356
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B40D010 ER8B40935 8LBS0WH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4191.0 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245356

CATALOG NUMBER: LD8B40D010 ER8B40935 8LBS0WH

Luminous Intensity Polar Plot





TEST NUMBER: P245356

CATALOG NUMBER: LD8B40D010 ER8B40935 8LBS0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	73199
5°	73479
10°	74407
15°	75861
20°	76942
25°	77259
30°	74892
35°	68358
40°	59129
45°	46548
50°	30026
55°	14736
60°	6062
65°	2656
70°	766
75°	286
80°	213
85°	0



TEST NUMBER: P245356

CATALOG NUMBER: LD8B40D010 ER8B40935 8LBS0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	226.7	5.4
10°-20°	671.6	16.0
20°-30°	1039.7	24.8
30°-40°	1126.4	26.9
40°-50°	810.5	19.3
50°-60°	271.2	6.5
60°-70°	41.0	1.0
70°-80°	3.5	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1937.9	46.2
0°-40°	3064.3	73.1
0°-60°	4146.0	98.9
0°-90°	4191.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4191.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2374	
5°	2374	227
15°	2376	672
25°	2271	1040
35°	1816	1126
45°	1067	811
55°	274	271
65°	36	41
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P245356

CATALOG NUMBER: LD8B40D010 ER8B40935 8LBS0WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2373.8
2.5°	2373.8
5°	2373.8
7.5°	2375.0
10°	2376.3
12.5°	2378.7
15°	2376.3
17.5°	2366.6
20°	2344.7
22.5°	2312.0
25°	2270.7
27.5°	2205.2
30°	2103.3
32.5°	1969.9
35°	1815.9
37.5°	1649.7
40°	1468.9
42.5°	1274.9
45°	1067.4
47.5°	843.0
50°	625.9
52.5°	429.4
55°	274.1
57.5°	163.8
60°	98.3
62.5°	59.4
65°	36.4
67.5°	18.2
70°	8.5
72.5°	3.6
75°	2.4
77.5°	2.4
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)