

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247846

Luminaire Tested: **LD8B200D010 ER8B200835 8LBMOLI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247846  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-90)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B200D010 ER8B200835 8LBM0LI  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 3500 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 22092.0 lumens  
Efficiency: N/A  
Efficacy: 98.9 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 223.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P247846

CATALOG NUMBER: LD8B200D010 ER8B200835 8LBM0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P247846

CATALOG NUMBER: LD8B200D010 ER8B200835 8LBM0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88
3	103	97	93	89	102	96	92	88	93	90	87	91	88	85	89	86	84	83
4	99	91	86	82	97	90	86	82	88	84	81	86	83	80	84	81	79	78
5	94	86	81	77	92	85	80	76	83	79	76	82	78	75	80	77	74	73
6	90	81	76	72	88	80	75	71	79	74	71	78	73	70	76	73	70	68
7	86	77	71	67	84	76	71	67	75	70	67	74	69	66	73	69	66	65
8	82	73	67	63	80	72	67	63	71	66	63	70	66	62	69	65	62	61
9	78	69	63	60	77	68	63	59	68	63	59	67	62	59	66	62	59	58
10	75	66	60	56	74	65	60	56	64	59	56	64	59	56	63	59	56	55

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1064396
5°	1033858
10°	914965
15°	777697
20°	647515
25°	523665
30°	389185
35°	242925
40°	119623
45°	50608
50°	18321
55°	5650
60°	3034
65°	1262
70°	1316
75°	322
80°	479
85°	0



TEST NUMBER: P247846

CATALOG NUMBER: LD8B200D010 ER8B200835 8LBM0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	3054.7	13.8
10°-20°	6775.9	30.7
20°-30°	6999.6	31.7
30°-40°	4080.6	18.5
40°-50°	1022.6	4.6
50°-60°	123.9	0.6
60°-70°	25.9	0.1
70°-80°	3.3	0.0
80°-90°	5.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	16830.2	76.2
0°-40°	20910.8	94.7
0°-60°	22057.3	99.8
0°-90°	22092.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	22092.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	34518	
5°	33400	###
15°	24361	6776
25°	15391	7000
35°	6453	4081
45°	1160	1023
55°	105	124
65°	17	26
75°	3	3
85°	0	5
90°	0	



TEST NUMBER: P247846

CATALOG NUMBER: LD8B200D010 ER8B200835 8LBM0LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	34517.6
2.5°	34250.1
5°	33399.7
7.5°	31725.5
10°	29220.9
12.5°	26740.3
15°	24360.8
17.5°	21973.3
20°	19732.1
22.5°	17578.9
25°	15391.0
27.5°	13215.1
30°	10930.1
32.5°	8675.7
35°	6453.2
37.5°	4534.1
40°	2971.7
42.5°	1872.5
45°	1160.5
47.5°	708.0
50°	381.9
52.5°	186.3
55°	105.1
57.5°	57.2
60°	49.2
62.5°	34.6
65°	17.3
67.5°	21.3
70°	14.6
72.5°	0.0
75°	2.7
77.5°	1.3
80°	2.7
82.5°	4.0
85°	0.0
87.5°	14.6
90°	0.0

(END OF REPORT)