

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249804

Luminaire Tested: **LD8B200D010 ER8B200835 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P249804
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13959)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B200D010 ER8B200835 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 18967.0 lumens
Efficiency: N/A
Efficacy: 84.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.81
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 223.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P249804

CATALOG NUMBER: LD8B200D010 ER8B200835 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P249804

CATALOG NUMBER: LD8B200D010 ER8B200835 8LBNOH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	65	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	55	63	58	54		62	57	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	802191
5°	792341
10°	731762
15°	638080
20°	546579
25°	457519
30°	348073
35°	215769
40°	106452
45°	50665
50°	24634
55°	12075
60°	7524
65°	5151
70°	2894
75°	2299
80°	2273
85°	2264



TEST NUMBER: P249804

CATALOG NUMBER: LD8B200D010 ER8B200835 8LBNOH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2372.2	12.5
10°-20°	5569.3	29.4
20°-30°	6087.0	32.1
30°-40°	3622.3	19.1
40°-50°	993.6	5.2
50°-60°	225.1	1.2
60°-70°	69.5	0.4
70°-80°	21.1	0.1
80°-90°	7.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	14028.5	74.0
0°-40°	17650.7	93.1
0°-60°	18869.4	99.5
0°-90°	18967.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	18967.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	26014	
5°	25597	###
15°	19987	5569
25°	13447	6087
35°	5732	3622
45°	1162	994
55°	225	225
65°	71	70
75°	19	21
85°	6	7
90°	0	



TEST NUMBER: P249804

CATALOG NUMBER: LD8B200D010 ER8B200835 8LBNOH

CANDELA DISTRIBUTION (FULL):

	0°
0°	26014.5
1°	26065.8
2°	26033.7
3°	25969.5
4°	25821.9
5°	25597.3
6°	25308.4
7°	24923.3
8°	24474.0
9°	23954.1
10°	23370.0
11°	22747.4
12°	22079.9
13°	21393.1
14°	20680.6
15°	19987.4
16°	19307.1
17°	18639.5
18°	17972.0
19°	17304.5
20°	16656.2
22.5°	15025.9
25°	13446.9
27.5°	11707.5
30°	9775.5
32.5°	7702.3
35°	5731.8
37.5°	3985.9
40°	2644.5
42.5°	1733.0
45°	1161.8
47.5°	770.2
50°	513.5
52.5°	314.5
55°	224.6
57.5°	160.5
60°	122.0
62.5°	89.9
65°	70.6
67.5°	44.9
70°	32.1
72.5°	25.7
75°	19.3
77.5°	12.8
80°	12.8



TEST NUMBER: P249804

CATALOG NUMBER: LD8B200D010 ER8B200835 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
82.5°	6.4
85°	6.4
87.5°	6.4
90°	0.0

(END OF REPORT)