

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247996

Luminaire Tested: **LD8B200D010 ER8B200850 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247996
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-71)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B200D010 ER8B200850 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 21362.0 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 223.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247996

CATALOG NUMBER: LD8B200D010 ER8B200850 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P247996

CATALOG NUMBER: LD8B200D010 ER8B200850 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74
4	93	84	77	72	91	82	76	72	80	75	71	78	74	70	76	72	69	67
5	87	77	70	65	85	76	70	65	74	68	64	72	67	64	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47
9	68	57	50	46	67	56	50	46	55	49	45	54	49	45	54	49	45	43
10	64	53	47	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	464827
5°	461677
10°	455533
15°	449935
20°	445511
25°	436189
30°	394608
35°	317420
40°	229592
45°	155139
50°	112914
55°	82621
60°	61272
65°	40817
70°	18113
75°	8197
80°	5754
85°	6687



TEST NUMBER: P247996

CATALOG NUMBER: LD8B200D010 ER8B200850 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1412.5	6.6
10°-20°	3977.9	18.6
20°-30°	5809.2	27.2
30°-40°	5224.5	24.5
40°-50°	2857.2	13.4
50°-60°	1416.5	6.6
60°-70°	559.4	2.6
70°-80°	90.1	0.4
80°-90°	14.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	11199.6	52.4
0°-40°	16424.1	76.9
0°-60°	20697.8	96.9
0°-90°	21362.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	21362.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15074	
5°	14915	###
15°	14094	3978
25°	12820	5809
35°	8432	5224
45°	3558	2857
55°	1537	1417
65°	559	559
75°	69	90
85°	19	15
90°	0	



TEST NUMBER: P247996

CATALOG NUMBER: LD8B200D010 ER8B200850 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	15074.0
2.5°	15032.2
5°	14914.9
7.5°	14762.6
10°	14548.2
12.5°	14320.4
15°	14093.9
17.5°	13851.3
20°	13576.3
22.5°	13262.2
25°	12820.0
27.5°	12075.9
30°	11082.4
32.5°	9830.0
35°	8432.1
37.5°	7036.9
40°	5703.6
42.5°	4502.5
45°	3557.5
47.5°	2851.1
50°	2353.7
52.5°	1915.6
55°	1536.8
57.5°	1241.6
60°	993.5
62.5°	785.9
65°	559.4
67.5°	333.0
70°	200.9
72.5°	113.2
75°	68.8
77.5°	44.5
80°	32.4
82.5°	10.8
85°	18.9
87.5°	8.1
90°	0.0

(END OF REPORT)