

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P248014

Luminaire Tested: **LD8B200D010 ER8B200927 8LBW0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P248014  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-71)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B200D010 ER8B200927 8LBW0WMH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 2700 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 16520.6 lumens  
Efficiency: N/A  
Efficacy: 74.0 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 223.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P248014

CATALOG NUMBER: LD8B200D010 ER8B200927 8LBW0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P248014

CATALOG NUMBER: LD8B200D010 ER8B200927 8LBW0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	86	84	82
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82	79	76	74
4	93	84	77	72	91	82	76	72	80	75	71		78	74	70		76	72	69	67
5	87	77	70	65	85	76	70	65	74	68	64		72	67	64		71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66	61	58	56
7	77	66	59	54	75	65	58	54	64	58	53		62	57	53		61	56	53	51
8	72	61	54	49	71	61	54	49	59	53	49		58	53	49		57	52	49	47
9	68	57	50	46	67	56	50	46	55	49	45		54	49	45		54	49	45	43
10	64	53	47	42	63	53	46	42	52	46	42		51	46	42		50	45	42	40

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P248014

CATALOG NUMBER: LD8B200D010 ER8B200927 8LBW0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1092.4	6.6
10°-20°	3076.4	18.6
20°-30°	4492.6	27.2
30°-40°	4040.4	24.5
40°-50°	2209.7	13.4
50°-60°	1095.5	6.6
60°-70°	432.6	2.6
70°-80°	69.7	0.4
80°-90°	11.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8661.4	52.4
0°-40°	12701.8	76.9
0°-60°	16007.0	96.9
0°-90°	16520.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	16520.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11658	
5°	11535	###
15°	10900	3076
25°	9914	4493
35°	6521	4040
45°	2751	2210
55°	1188	1095
65°	433	433
75°	53	70
85°	15	11
90°	0	



TEST NUMBER: P248014

CATALOG NUMBER: LD8B200D010 ER8B200927 8LBW0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	11657.7
2.5°	11625.4
5°	11534.6
7.5°	11416.8
10°	11251.1
12.5°	11074.9
15°	10899.8
17.5°	10712.1
20°	10499.4
22.5°	10256.5
25°	9914.5
27.5°	9339.1
30°	8570.7
32.5°	7602.2
35°	6521.1
37.5°	5442.1
40°	4411.0
42.5°	3482.1
45°	2751.3
47.5°	2205.0
50°	1820.2
52.5°	1481.4
55°	1188.4
57.5°	960.2
60°	768.4
62.5°	607.8
65°	432.7
67.5°	257.5
70°	155.4
72.5°	87.5
75°	53.2
77.5°	34.4
80°	25.0
82.5°	8.3
85°	14.6
87.5°	6.3
90°	0.0

(END OF REPORT)